





# 4-CONDUCTOR TERMINAL STRIP LATERAL MARKING WITH SNAP-IN MOUNTING FOOT

260-252 TO 260-262

<b>ITEM-NO. (ITEM-NO.)</b>	260-252
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 1.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 16
<b>Strip length (Strip length / mm)</b>	8 - 9
<b>Measured voltage (Measured voltage / V)</b>	400
<b>Measured shock voltage (Measured shock voltage / kV)</b>	6
<b>Pollution degree (Pollution degree)</b>	3
<b>Current intensity (Current intensity / A)</b>	18
<b>P (NO. OF POLES)</b>	2
<b>Height (Height / mm)</b>	17
<b>Width (Width / mm)</b>	20.4
<b>Depth (Depth / mm)</b>	25
<b>No. of connection Points (No. of connection Points)</b>	8
<b>No. of potentials (No. of potentials)</b>	2
<b>COLOR (COLOR)</b>	grau
<b>WEIGHT (WEIGHT / g)</b>	6.13
<b>Comment (Comment)</b>	L = (No. of poles x pole width) + 4,4 mm