



ITEM-NO. (ITEM-NO.)	262-103
Cross section1 (Cross section / mm²)	0.08 - 4
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	9 - 10
Measured voltage (Measured voltage / V)	630
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	24
RM (PIN SPACING / mm)	
P (NO. OF POLES)	3
Height (Height / mm)	23
Width (Width / mm)	35.5
Depth (Depth / mm)	33.5
No. of connection Points (No. of connection Points)	6
No. of potentials (No. of potentials)	3
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	2.1
Comment (Comment)	L = No. of poles x pole width L1 = L + 8.1 mm L2 = L+14.5 mm