



| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 262-108 |
| Cross section1 (Cross section / mm²) | 0.08 - 4 |
| Cross section2 (Cross section / AWG) | 28 - 12 |
| Strip length (Strip length / mm) | 9 - 10 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 8 |
| Pollution degree (Pollution degree) | 3 |
| Current intensity (Current intensity / A) | 24 |
| RM (PIN SPACING / mm) | |
| P (NO. OF POLES) | 8 |
| Height (Height / mm) | 23 |
| Width (Width / mm) | 70.5 |
| Depth (Depth / mm) | 33.5 |
| No. of connection Points (No. of connection Points) | 16 |
| No. of potentials (No. of potentials) | 8 |
| COLOR (COLOR) | grau |
| WEIGHT (WEIGHT / g) | 35.05 |
| Comment (Comment) | L = No. of poles x pole width L1 = L + 8.1 mm L2 = L+14.5 mm |