



SPECIFICATION FOR:

() REF.:

P/N: EC24R33K-502406-T	DATE: DD/MM/YYYY 18-01-2014	
PRODUCT NAME: EC24TB-R33K-VER00		

1.DIMENSION (UNIT : mm):



A: 7.0 Max.	B: 52.4 ± 1.5	C: 6.0 ± 1.0	D: 3.2 Min.	E: 0.50 ± 0.05
F: 5.0 ± 0.5	G: 1.0 Max.	H: 3.0 Max.	I: 1.0 Max.	J:

2.ELECTRIC CHARACTERISTICS: (TEST AT : 24°C ± 4°C)

INDUCTANCE: 0.33uH ± 10%	TEST FREQ: @ 25.2MHz	DCR: 0.15 Ω Max
TURNS: 4.5 TS (Ref)	IDC: ----- A	RDC: 1.11A
Q: 40 Min @ 25.2 MHz	SRF: 260 MHz Min.	TEMP: -20°C ~ +80°C

3.TEST EQUIPMENT:

- | | | |
|---|--|--|
| <input type="checkbox"/> HP-4284A (LCZ-METER) | <input type="checkbox"/> CH-1062 (LCZ-METER) | <input checked="" type="checkbox"/> CH-1320(CURRENT METER) |
| <input type="checkbox"/> HP-8712C (ANALYZER) | <input type="checkbox"/> SK-3005 (INSULATION TESTER) | <input checked="" type="checkbox"/> MQ-1601 (Q-METER) |
| <input type="checkbox"/> CH-100 (LCR-METER) | <input type="checkbox"/> CH-852A (HIGH POT TEST METER) | <input type="checkbox"/> HL-2801 (ANALYZER) |
| <input checked="" type="checkbox"/> HK502BC (DCR-METER) | <input checked="" type="checkbox"/> HM-9461(L-SRF METER) | <input type="checkbox"/> |

4. MATERIALS: [2.5] [6]

CORE: 06-H DRWW 2.3 X 4 (B:1.4 F:1.8)	PIN: CP-1
WIRE: φ 0.12mm 2 UEW 130°C	0.026kg/kpcs
SLEEVE: --- mm x --- mm --- (MARK'G: --- COLOR: ---)	---m/kpcs
VARNISH: -----	BOBBIN & BASE: -----
COATING: EPOXY#2030	N.W: 0.179 kg/kpcs
	PACKING: 3000PCS/BOX

5.NOTE: