



<b>ITEM-NO. (ITEM-NO.)</b>	264-241
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.5 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	20 - 12
<b>Strip length (Strip length / mm)</b>	8 - 9
<b>Measured voltage (Measured voltage / V)</b>	690
<b>Measured shock voltage (Measured shock voltage / kV)</b>	
<b>Pollution degree (Pollution degree)</b>	
<b>Current intensity (Current intensity / A)</b>	23
<b>P (NO. OF POLES)</b>	11
<b>Height (Height / mm)</b>	22.1
<b>Width (Width / mm)</b>	126
<b>Depth (Depth / mm)</b>	32
<b>No. of connection Points (No. of connection Points)</b>	44
<b>No. of potentials (No. of potentials)</b>	11
<b>COLOR (COLOR)</b>	lichtgrau
<b>WEIGHT (WEIGHT / g)</b>	75.48
<b>Comment (Comment)</b>	L = (No. of poles x pole width)   L1 = L + 9,6 mm   L2 = L + 16 mm