


## Product Description

Seawater-resistant; Anti-magnetic; Corrosion-resistant; Stable and safe strain relief



## Application range

- Extremely robust and solid strain relief cable gland.
- Building sites
- Plant engineering
- Electric motor manufacturing

## Benefits

- Seawater-resistant
- Anti-magnetic
- Corrosion-resistant
- Stable and safe strain relief

## Design

- PG connection thread

## Note

- Counter nut to be used: SKINDICHT® SM



Technical Data

**Caution**

The installation dimensions can be found in appendix T21

**Upon request**

Available with long connection thread

**Material**

Body: nickel-plated brass

**Protection rating**

IP 20

Article List

Part number	Article designation / size	Clamping range ØF (mm)	SW (mm)	Max. fitting size for installation (mm)	Overall length/ C (mm)	Thread length/ D (mm)	Pieces / PU
SKINDICHT® SH							
52000830	SH 7	8 - 10	15	22	17,5	5.5	50
52000840	SH 9	10 - 12,5	17	25	20,5	6.0	50
52000850	SH 11	11 - 15	20	28	21,5	6.0	50
52000860	SH 13,5	14 - 16,5	22	32	24.0	7.5	25
52000870	SH 16	15 - 18	24	35	26.0	7.5	25
52000880	SH 21	18 - 23,5	30	46	29.0	8.0	25
52000890	SH 29	23 - 31	41	58	33.0	8.0	10
52000900	SH 36	29 - 40,5	50	70	36,5	9.5	10
52000910	SH 42	34 - 45	57	78	38.0	10.0	5
52000920	SH 48	39 - 50	64	86	39,5	11.5	5

**Footnote:**

Photographs are not to scale and do not represent detailed images of the respective products.