



|   |  |
|---|--|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 264-232  |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.5 - 2.5  |
| <b>Cross section2 (Cross section / AWG)</b>                 | 20 - 12  |
| <b>Strip length (Strip length / mm)</b>                     | 8 - 9  |
| <b>Measured voltage (Measured voltage / V)</b>              | 690  |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> |  |
| <b>Pollution degree (Pollution degree)</b>                  |  |
| <b>Current intensity (Current intensity / A)</b>            | 23   |
| <b>P (NO. OF POLES)</b>                                     | 2  |
| <b>Height (Height / mm)</b>                                 | 22.1   |
| <b>Width (Width / mm)</b>                                   | 36   |
| <b>Depth (Depth / mm)</b>                                   | 32   |
| <b>No. of connection Points (No. of connection Points)</b>  | 8  |
| <b>No. of potentials (No. of potentials)</b>                | 2  |
| <b>COLOR (COLOR)</b>  | lichtgrau  |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 14.68  |
| <b>Comment (Comment)</b>                                    | L = (No. of poles x pole width)   L1 = L + 9,6 mm   L2 = L + 16 mm |