

**VG K (standard plastic cable gland)
VG PG7-K67**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Cable glands for professional use in industrial applications which meet the highest demands in terms of quality and safety. They are available made from polyamide, polystyrene and brass.

General ordering data

Type	VG PG7-K67
Order No.	1909760000
Version	VG K (standard plastic cable gland), Cable glands, PG 7, 8 mm, OD min. 3 - OD max. 6.5 mm, Polyamide 6
GTIN (EAN)	4032248536689
Qty.	100 pc(s).

**VG K (standard plastic cable gland)
VG PG7-K67**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Length	30 mm	Length (inches)	1.181 inch
Net weight	3.4 g		

General information

AF size 1	15 mm	Cable glands	PG
External thread	PG 7	Length of thread	8 mm
Material	Polyamide 6	Operating temperature range, max.	100 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	6.5 mm
Outer cable diameter, min.	3 mm	Protection degree	IP67
Seal insert	NBR	Torque for cap nut, max.	2.5 Nm
Torque for cap nut, min.	1.5 Nm	Torque for connecting adapter, max.	1.8 Nm
Torque for connecting adapter, min.	1.2 Nm	UL 94 flammability rating	V-2

Classifications

ETIM 3.0	EC000441	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000441
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-09
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-14-44-32
eClass 9.1	27-14-44-32		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	CAT 3 HDC 17/18 EN CAT 5 ENCL 17/18 EN
Engineering Data	EPLAN, WSCAD
Engineering Data	STEP