



|   |                               |
|---|-------------------------------|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 280-904                       |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.08 - 2.5                    |
| <b>Cross section2 (Cross section / AWG)</b>                 | 28 - 12                       |
| <b>Strip length (Strip length / mm)</b>                     | 8 - 9                         |
| <b>Measured voltage (Measured voltage / V)</b>              | 800                           |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 8                             |
| <b>Pollution degree (Pollution degree)</b>                  | 3                             |
| <b>Current intensity (Current intensity / A)</b>            | 24                            |
| <b>Height (Height / mm)</b>                                 | 28                            |
| <b>Width (Width / mm)</b>                                   | 5                             |
| <b>Depth (Depth / mm)</b>                                   | 53                            |
| <b>No. of connection Points (No. of connection Points)</b>  | 2                             |
| <b>No. of potentials (No. of potentials)</b>                | 1                             |
| <b>COLOR (COLOR)</b>  | blau                          |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 5.428                         |
| <b>Comment (Comment)</b>                                    | Für Ex i-Anwendungen geeignet |