



ITEM-NO. (ITEM-NO.)	283-904
Cross section1 (Cross section / mm²)	0.2 - 16
Cross section2 (Cross section / AWG)	24 - 06
Strip length (Strip length / mm)	16 - 17
Measured voltage (Measured voltage / V)	800
Measured shock voltage (Measured shock voltage / kV)	8
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	76
Height (Height / mm)	37.5
Width (Width / mm)	12
Depth (Depth / mm)	94.5
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	1
COLOR (COLOR)	blau
WEIGHT (WEIGHT / g)	35.755
Comment (Comment)	