



ITEM-NO. (ITEM-NO.)	283-998
Cross section1 (Cross section / mm²)	0.5 - 16
Cross section2 (Cross section / AWG)	20 - 06
Strip length (Strip length / mm)	16 - 17
Measured voltage (Measured voltage / V)	550
Measured shock voltage (Measured shock voltage / kV)	
Pollution degree (Pollution degree)	
Current intensity (Current intensity / A)	68
Height (Height / mm)	37.5
Width (Width / mm)	12
Depth (Depth / mm)	104.5
No. of connection Points (No. of connection Points)	3
No. of potentials (No. of potentials)	1
COLOR (COLOR)	lichtgrau
WEIGHT (WEIGHT / g)	46.052
Comment (Comment)	für Ex e II-Anwendungen geeignet