





FEMALE PLUG PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING

713-1103 TO 713-1118

PDF DATASHEET

© 1992 - 2011 CADENAS GmbH

ITEM-NO. (ITEM-NO.)	713-1104
Cross section1 (Cross section / mm ²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 16
Strip length (Strip length / mm)	6 - 7
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	8
Height (Height / mm)	18.8
Width (Width / mm)	15.5
Depth (Depth / mm)	16
No. of connection Points (No. of connection Points)	8
No. of potentials (No. of potentials)	8
COLOR (COLOR)	schwarz
Comment (Comment)	$L = ((\text{No. of poles} / 2) - 1) \times \text{Pin Spacing} + 5$ mm