



|   |  |
|---|--|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 721-2116/026-000                             |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.2 - 2.5                                    |
| <b>Cross section2 (Cross section / AWG)</b>                 | 24 - 12                                      |
| <b>Strip length (Strip length / mm)</b>                     | 9 - 10                                       |
| <b>Measured voltage (Measured voltage / V)</b>              | 320  |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 4  |
| <b>Pollution degree (Pollution degree)</b>                  | 2  |
| <b>Current intensity (Current intensity / A)</b>            | 16   |
| <b>RM (PIN SPACING / mm)</b>                                | 5  |
| <b>P (NO. OF POLES)</b>                                     | 16   |
| <b>Height (Height / mm)</b>                                 | 20.8   |
| <b>Width (Width / mm)</b>                                   | 80   |
| <b>Depth (Depth / mm)</b>                                   | 26.45  |
| <b>No. of connection Points (No. of connection Points)</b>  | 32   |
| <b>No. of potentials (No. of potentials)</b>                | 16   |
| <b>COLOR (COLOR)</b>  | lichtgrau                                    |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 36.618                                       |
| <b>Comment (Comment)</b>                                    | L = (No. of poles - 2) x Pin Spacing + 10 mm |