





**MALE CONNECTOR PIN SPACING 5
MM / 0.197 IN 100% PROTECTED
AGAINST MISMATING
721-602 TO 721-620**

ITEM-NO. (ITEM-NO.)	721-608
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	8
Height (Height / mm)	14.3
Width (Width / mm)	43.2
Depth (Depth / mm)	27.5
No. of connection Points (No. of connection Points)	8
No. of potentials (No. of potentials)	8
COLOR (COLOR)	lichtgrau
Comment (Comment)	A = (No. of poles x Pin Spacing) + 3,2 mm B = A - 1,7 mm C = A - 1,2 mm