



### Cable Ties inside serrated

- RELK-Series up to 200 N loop tensile strength
- RLT-Series up to 670N loop tensile strength

#### Features and Benefits

The extended pawl allows for the quick and simple release of the ties. Manufactured in various grades of PA66 these products are suitable for indoor, outdoor and high temperature applications.

#### Application

Used in a wide range of industries these releasable and reusable ties are ideal where temporary installation, or, the addition or removal of cables is required, e.g. Theatres, outdoor events or prototype harnessing work.




The RELK and RLT cable ties can be re-opened and re-used.


Material Data	
Material	<b>Polyamide 6.6 UV Resistant (PA66W)</b>
Operating Temperature	<b>-40 °C to +85 °C Continuous, (+105 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



Material Data	
Material	<b>Polyamide 6.6 Heat Stabilised (PA66HS)</b>
Operating Temperature	<b>-40 °C to +105 °C Continuous, (+145 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



 **Material specification please see page 64.**



RELK-, RLT-Serie

Technical Table							
Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Material	Colour
115-02202	RELK2R	200	4.6	50.0	200	PA66	Natural (NA)
115-02200	RELK2R	200	4.6	50.0	200	PA66	Black (BK)
115-06729	RELK2M	250	4.6	65.0	200	PA66	Natural (NA)
115-02000	RELK2M	250	4.6	65.0	200	PA66	Black (BK)
115-02101	RELK2I	300	4.6	81.0	200	PA66	Natural (NA)
115-06760	RELK2I	300	4.6	81.0	200	PA66	Black (BK)
115-06919	RELK2L	350	4.6	95.0	200	PA66	Natural (NA)
115-02300	RELK2L	350	4.6	95.0	200	PA66	Black (BK)
111-70319	RLT120	340	7.6	90.0	535	PA66	Natural (NA)
111-70361	RLT120	340	7.6	90.0	535	PA66	Black (BK)
111-70119	RLT150	770	8.9	225	670	PA66	Natural (NA)
111-70110	RLT150	770	8.9	225	670	PA66	Black (BK)
111-70160	RLT150	770	8.9	225	670	PA66W	Black (BK)
111-70159	RLT150	770	8.9	225	670	PA66HS	Natural (NA)

All dimensions in mm. Subject to technical changes.



® Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.