



**1-CONDUCTOR-FEEDTHROUGH  
TERMINAL BLOCK FOR FLUSH-  
MOUNTING PIN SPACING 5 MM / 0.197  
IN  
731-132 TO 731-142/048-000**

<b>ITEM-NO. (ITEM-NO.)</b>	731-139/048-000
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 14
<b>Strip length (Strip length / mm)</b>	8 - 9
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	5
<b>RM (PIN SPACING / mm)</b>	5
<b>P (NO. OF POLES)</b>	9
<b>Height (Height / mm)</b>	12
<b>Width (Width / mm)</b>	60.2
<b>Depth (Depth / mm)</b>	15.5
<b>No. of connection Points (No. of connection Points)</b>	9
<b>No. of potentials (No. of potentials)</b>	9
<b>COLOR (COLOR)</b>	grau
<b>WEIGHT (WEIGHT / g)</b>	14.077
<b>Comment (Comment)</b>	L = (No. of poles x Pin Spacing) + 3 mm   L1 = L + 5,8 mm   L2 = L + 6,4 mm
<b>Dimensions (Dimensions)</b>	For thickness of mounting plate 1,5 mm max