



**1-CONDUCTOR-FEEDTHROUGH  
TERMINAL BLOCK FOR FLUSH-  
MOUNTING PIN SPACING 5 MM / 0.197  
IN  
731-132 TO 731-142/048-000**

|   |   |
|---|---|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 731-133   |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.08 - 2.5  |
| <b>Cross section2 (Cross section / AWG)</b>                 | 28 - 14   |
| <b>Strip length (Strip length / mm)</b>                     | 8 - 9   |
| <b>Measured voltage (Measured voltage / V)</b>              | 320   |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 4   |
| <b>Pollution degree (Pollution degree)</b>                  | 2   |
| <b>Current intensity (Current intensity / A)</b>            | 5   |
| <b>RM (PIN SPACING / mm)</b>                                | 5   |
| <b>P (NO. OF POLES)</b>                                     | 3   |
| <b>Height (Height / mm)</b>                                 | 12  |
| <b>Width (Width / mm)</b>                                   | 30.2  |
| <b>Depth (Depth / mm)</b>                                   | 15.5  |
| <b>No. of connection Points (No. of connection Points)</b>  | 3   |
| <b>No. of potentials (No. of potentials)</b>                | 3   |
| <b>COLOR (COLOR)</b>  | grau  |
| <b>WEIGHT (WEIGHT / g)</b>                                  | 5.159   |
| <b>Comment (Comment)</b>                                    | L = (No. of poles x Pin Spacing) + 3 mm   L1 = L + 5,8 mm   L2 = L + 6,4 mm |
| <b>Dimensions (Dimensions)</b>                              | For thickness of mounting plate 1,5 mm max                                  |