





**Male connector pin spacing 7.5 mm /
0.295 in**
731-602 TO 731-616

PDF DATASHEET

© 1992 - 2011 | CADENAS GmbH

| | |
|---|--|
| ITEM-NO. (ITEM-NO.) | 731-611 |
| Cross section1 (Cross section / mm²) | 0.08 - 2.5 |
| Cross section2 (Cross section / AWG) | 28 - 12 |
| Strip length (Strip length / mm) | 8 - 9 |
| Measured voltage (Measured voltage / V) | 630 |
| Measured shock voltage (Measured shock voltage / kV) | 6 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 7.5 |
| P (NO. OF POLES) | 11 |
| Height (Height / mm) | 14.3 |
| Width (Width / mm) | 83.2 |
| Depth (Depth / mm) | 27.5 |
| No. of connection Points (No. of connection Points) | 11 |
| No. of potentials (No. of potentials) | 11 |
| COLOR (COLOR) | grau |
| Comment (Comment) | L = (No. of poles - 1) x Pin Spacing + 8.2 mm L1 = L - 1.7 mm L2 = L - 1.2 mm |