



|   |  |
|---|--|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 731-632/019-000  |
| <b>Cross section1 (Cross section / mm<sup>2</sup>)</b>      | 0.08 - 2.5   |
| <b>Cross section2 (Cross section / AWG)</b>                 | 28 - 12  |
| <b>Strip length (Strip length / mm)</b>                     | 8 - 9  |
| <b>Measured voltage (Measured voltage / V)</b>              | 630  |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 6  |
| <b>Pollution degree (Pollution degree)</b>                  | 2  |
| <b>Current intensity (Current intensity / A)</b>            | 12   |
| <b>RM (PIN SPACING / mm)</b>                                | 7.62   |
| <b>P (NO. OF POLES)</b>                                     | 2  |
| <b>Height (Height / mm)</b>                                 | 14.3   |
| <b>Width (Width / mm)</b>                                   | 27.5   |
| <b>Depth (Depth / mm)</b>                                   | 27.5   |
| <b>No. of connection Points (No. of connection Points)</b>  | 2  |
| <b>No. of potentials (No. of potentials)</b>                | 2  |
| <b>COLOR (COLOR)</b>  | orange   |
| <b>Comment (Comment)</b>                                    | L = (No. of poles - 1) x Pin Spacing + 8.2 mm  <br>L3 = L - 0.2 mm   L4 = L3 + 5.8 mm   L5 = L3<br>+ 11.8 mm |