



ITEM-NO. (ITEM-NO.)	734-316
Cross section1 (Cross section / mm²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	7
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	16
Height (Height / mm)	13.4
Width (Width / mm)	58.4
Depth (Depth / mm)	22.3
No. of connection Points (No. of connection Points)	16
No. of potentials (No. of potentials)	16
COLOR (COLOR)	lichtgrau
Comment (Comment)	L4 = (No. of poles - 1) x Pin Spacing + 5,9 mm L5 = L4 + 0,45 mm