



**MALE CONNECTOR WITH FIXING  
FLANGE PIN SPACING 3.5 MM / 0.138  
IN 100% PROTECTED AGAINST  
MISMATING**

734-302/019-000 TO 734-324/019-000

<b>ITEM-NO. (ITEM-NO.)</b>	734-316/019-000
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.08 - 1.5
<b>Cross section2 (Cross section / AWG)</b>	28 - 14
<b>Strip length (Strip length / mm)</b>	7
<b>Measured voltage (Measured voltage / V)</b>	160
<b>Measured shock voltage (Measured shock voltage / kV)</b>	2.5
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	10
<b>RM (PIN SPACING / mm)</b>	3.5
<b>P (NO. OF POLES)</b>	16
<b>Height (Height / mm)</b>	13.4
<b>Width (Width / mm)</b>	70.8
<b>Depth (Depth / mm)</b>	22.3
<b>No. of connection Points (No. of connection Points)</b>	16
<b>No. of potentials (No. of potentials)</b>	16
<b>COLOR (COLOR)</b>	lichtgrau
<b>WEIGHT (WEIGHT / g)</b>	14.337
<b>Comment (Comment)</b>	L1 = (No. of poles - x Pin Spacing)   L2 = L1 + 8,8 mm   L3 = L1 + 14,8 mm   L4 = (No. of poles - 1) x Pin Spacing + 5,9 mm