



2-Piece Fixing Ties with Arrowhead, with Disc

Features and Benefits

These two piece fixing ties are supplied ready assembled and offer a simple and versatile method of bundling and fixing cables, pipes and hoses.

The arrowhead base will easily push into pre-punched holes in panels and offers a very secure fixing. The two piece design enables the head of the tie to be orientated to the required position to ease assembly, whilst the 'disc' on the top of the arrowhead takes up variation in panel thickness ensuring a stable fixing at all times.

Available as either inside serrated or outside serrated 'standard' cable ties or 'double headed' ties.

Application

Primarily designed for fixing cable harnesses in the automotive industry, their simplicity and ease of use has resulted in these parts being used in other industries, for example: aviation, switch-gear manufacturers, white goods manufacturers.



Being a two piece assembly allows the tie head to be located in the most convenient position.

Material Data

Material	Polyamide 6.6 High Imp. Mod., Heat Stab. (PA66HIRHS)
Colour	Black (BK)
Operating Temperature	-40 °C to +105 °C
Flammability	UL94 HB



Material Data

Material	Polyamide 6.6 Heat Stabilised (PA66HS)
Colour	Black (BK)
Operating Temperature	-40 °C to +105 °C continuous, (+145 °C for 500 h)
Flammability	UL94 V2



Technical Table

Article-No.	Type30	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile strength for ties (N)	Disc Ø	Hole Ø	Panel Thickness min.	Panel Thickness max.	Material Cable Tie	Material Foot Part
-------------	--------	------------	-----------	---------------	------------------------------------	--------	--------	----------------------	----------------------	--------------------	--------------------

2-Pieces Fixing Ties with Arrowhead, with Disc, sealed


150-37799	T50ROSSFT6.5 16-3MD	200	4.6	45.0	225	16.0	6.3-6.7	2.5	3.5	PA66HS	PA66HIRHS
150-93100	T50ROSSFT6,5ZD 16-2	200	4.6	45.0	225	22,4	6.3-6.7	0.7	2.0	PA66HS	PA66HIRHS

All dimensions in mm. Subject to technical changes.



2-Piece Fixing Ties with Arrowhead, with Disc

Other dimensions available, please contact us for further information.



Two piece fixing tie with moveable arrowhead

Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile strength for ties (N)	Disc Ø	Hole Ø	Panel Thickness min.	Panel Thickness max.	Material Cable Tie	Material Foot Part
150-13593	T50SSFT6.5	150	4.6	31.0	225	22.4	6.3-6.7	0.7	2.0	PA66HS	PA66HS
150-13591	T50RSFT6.5	200	4.6	45.0	225	22.4	6.3-6.7	0.9	2.0	PA66HS	PA66HS
117-05160	T50RDHSFT6.5	210	4.7	45.0	225	22.4	6.3-6.7	0.7	2.0	PA66HS	PA66HS
150-13596	T80ISFT6.5	300	4.6	81.0	355	22.4	6.3-6.7	0.7	2.0	PA66HS	PA66HS
150-13599	T50ROSSFT6.5	200	4.6	45.0	225	22.4	6.3-6.7	0.7	2.0	PA66HS	PA66HS
150-37691	T50RSFT6.5D18	200	4.6	45.0	225	18.0	6.5-6.8	0.4	1.6	PA66HS	PA66HIRHS
150-37791	T50ROS-SFT6,5 16-3	200	4.6	45.0	225	16.0	6.3-6.7	2.5	3.5	PA66HS	PA66HIRHS
150-37792	T50RSFT6,5 16-3	200	4.6	45.0	225	16.0	6.3-6.7	2.5	3.5	PA66HS	PA66HIRHS
150-93130	T50SOSFT65162OD	150	4.6	35.0	225	16.0	6,3-6,7	1.5	2.2	PA66HS	PA66HIRHS
155-42002	T50ROSSFT6,5-16-2-BK	200	4.6	45.0	225	16.0	6,3-6,7	0.7	1.2	PA66HS	PA66HIRHS

All dimensions in mm. Subject to technical changes.

2-Pieces Fixing Ties with Arrowhead, for Oval Holes

Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile strength for ties (N)	Hole Ø	Panel Thickness min.	Panel Thickness max.	Material Cable Tie	Material Foot Part
156-00446	T50RFT62x122HR	200	4.6	45.0	225	6.3x12.2	0.6	3.0	PA66HS	PA66HIRHS


All dimensions in mm. Subject to technical changes.

2-Pieces Fixing Ties with Arrowhead, for parallel routing

Technical Table

Article-No.	Type	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile strength for ties (N)	Hole Ø	Panel Thickness min.	Panel Thickness max.	Material Cable Tie	Material Foot Part
156-00133	T50SOSDSFT6.5	150	4.6	35.0	225	6.3-6.7	0.7	1.5	PA66HS	PA66HIRHS

All dimensions in mm. Subject to technical changes.



Being a two piece assembly allows the tie head to be located in the most convenient position