



**COMBI STRIP PIN AND SOCKET
CONNECTION PIN SPACING 3.5 MM /
0.138 IN 100% PROTECTED AGAINST
MISMATING**

734-362 TO 734-372

ITEM-NO. (ITEM-NO.)	734-365
Cross section1 (Cross section / mm²)	0.08 - 1.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	6 - 7
Measured voltage (Measured voltage / V)	160
Measured shock voltage (Measured shock voltage / kV)	2.5
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	10
RM (PIN SPACING / mm)	3.5
P (NO. OF POLES)	5
Height (Height / mm)	18.5
Width (Width / mm)	20.35
Depth (Depth / mm)	40.9
No. of connection Points (No. of connection Points)	10
No. of potentials (No. of potentials)	5
COLOR (COLOR)	lichtgrau
Comment (Comment)	L1 = No. of poles x Pin Spacing L4 = (No. of poles - 1) x Pin Spacing + 5,9 mm L5 = L4 + 0,45 mm