



### Mounting Plates for Screw Fixing


- **MP-Series for M3 screws**
- **MSMP-Series for M5 screws**

#### Features and Benefits


Allowing multiple cables to be run in parallel these mounting plates are simply fixed by two screws. The cables are attached to the mounting plate by using a cable tie through any combination of the available slots.

#### Application

Many applications require each cable run to be firmly held in place but separately from adjacent cable runs (example - control cabinets, machinery and military systems). The MP series of mounts help achieve this.



Mounting Plates Types MP and MSMP



Mounting Plates Types MP and MSMP

#### Material Data

Material	<b>Polyamide 6.6 (PA66)</b>
Colour	<b>Natural (NA)</b>
Operating Temperature	<b>-40 °C to +85 °C Continuous, (+105 °C for 500 h)</b>
Flammability	<b>UL94 V2</b>



#### Technical Table

Article-No.	Type	Length (L)	Width (W)	Height (H)	Fixing Hole Ø (FH)	Fixing Hole Centres (F)	Hole Size (HS)	Strap Width max. (G)	Material	No. of bundles
151-24219	<b>MP2M3</b>	76.2	12.7	3.2	3.7	31.8	6.4	5.2	PA66	2
151-24319	<b>MP3M3</b>	108.0	12.7	3.2	3.7	31.8	6.4	5.2	PA66	3
151-24419	<b>MP4M3</b>	139.8	12.7	3.2	3.7	31.8	6.4	5.2	PA66	4
150-83499	<b>MSMP4</b>	167.0	15.9	5.2	5.1	19.0	7.6	8.2	PA66	4
151-24519	<b>MP5M3</b>	171.6	12.7	3.2	3.7	31.8	6.4	5.2	PA66	5
151-25519	<b>MSMP5</b>	204.0	15.7	5.3	5.1	38.0	7.7	8.2	PA66	5
151-25619	<b>MSMP6</b>	242.0	15.7	5.3	3.5	38.0	7.7	8.2	PA66	6

All dimensions in mm. Subject to technical changes.



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.