



### Heat Shrinkable Tubing 6:1, adhesive lined in 1 m cuts

- HA67

#### Features and Benefits


High shrink-ratio heavy-duty heat shrinkable tubing designed to pass over large size connectors and shrink down onto much smaller cable jackets. The thermoplastic adhesive lined tubing provides environmental sealing, excellent insulation and resistance to impact and abrasion. The 6:1 shrink-ratio conforms well to highly variable substrate dimensions and simplifies cable repair.

#### Application

Insulates, seals and protects large size differences between connectors and cables.



Due to the high shrink ratio HA67 is suitable for complex shapes and dimensions.



HA67

Material Data	
Material	<b>Polyolefin, cross-linked (POX)</b>
Colour	<b>Black (BK)</b>
Shrink Ratio	<b>6:1</b>
Longitudinal change after shrinkage	<b>-10% max.</b>
Minimum Shrink Temperature	<b>+120 °C</b>
Operating Temperature	<b>-55 °C to +110 °C</b>
Softening Point Adhesive	<b>+85 °C</b>
Dielectric Strength	<b>20kV/mm according to ASTM D2671</b>



#### Technical Table

Article-No.	Type	Supplied Ø D	Recov. Ø d	Wall (WT) nom.	Length (L)
321-30000	<b>HA67-19.0/3.2</b>	19.0	3.2	3.2	1220
321-30100	<b>HA67-33.0/5.5</b>	33.0	5.5	3.4	1220
321-30200	<b>HA67-44.4/7.4</b>	44.4	7.4	3.6	1220
321-30300	<b>HA67-50.8/8.3</b>	50.8	8.3	4.8	1220
321-30400	<b>HA67-69.8/11.7</b>	69.8	11.7	4.8	1220
321-30500	<b>HA67-88.9/17.1</b>	88.9	17.1	4.8	1220
321-30600	<b>HA67-119.4/22.9</b>	119.4	22.9	4.8	1220
321-30700	<b>HA67-235.0/40.0</b>	235.0	40.0	4.8	1220

All dimensions in mm. Subject to technical changes.