

## Cable marker - UC-WMTB (44X15) YE - 0828379

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable marker, Sheet, yellow, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Assembly with cable binders, Cable diameter: >7 mm, Lettering field: 44 x 15 mm

### Product Features

- ✓ The UC-WMTB ... UniCard labeling range includes markers that can be secured using standard cable binders
- ✓ For large-surface labeling of conductors and cables > 7 mm in diameter
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ The sheets provide space for including function texts
- ✓ The format automatically ensures printing with a high degree of positioning accuracy

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 10            |
| GTIN             | 4046356485371 |

### Technical data

#### Dimensions

|           |       |
|-----------|-------|
| Width (a) | 44 mm |
|-----------|-------|

#### Ambient conditions

|                                 |                             |
|---------------------------------|-----------------------------|
| Wipe resistance                 | DIN EN 61010-1 (VDE 0411-1) |
| Ambient temperature (operation) | -40 °C ... 120 °C           |

#### General

|                                                                     |                                |
|---------------------------------------------------------------------|--------------------------------|
| Color                                                               | yellow                         |
| Components                                                          | free from silicone and halogen |
| Inflammability class according to UL 94                             | V2                             |
| Material                                                            | PA                             |
| Number of individual labels                                         | 4                              |
| Number of individual labels per row                                 | 1                              |
| Min. cross section                                                  | 16 mm <sup>2</sup>             |
| Printability                                                        | Inkjet printing                |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02           |
| Result                                                              | Test passed                    |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03   |

## Cable marker - UC-WMTB (44X15) YE - 0828379

### Technical data

#### General

|                                                              |                                     |
|--------------------------------------------------------------|-------------------------------------|
| Test duration                                                | 96 h                                |
| Wipe resistance test result                                  | Test passed                         |
| Salt spray test specification                                | DIN EN ISO 9227:2012-09             |
| Test duration                                                | 96 h                                |
| Salt spray testing result                                    | Test passed                         |
| Alternating condensation climate with SO2 test specification | DIN 50018:1997-06                   |
| Climate level                                                | KFW 1.0 S                           |
| Cycles                                                       | 2                                   |
| Condensation test result                                     | Test passed                         |
| Wipe resistance of test specification inscriptions           | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result                                                       | Test passed                         |

### classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27400401 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400401 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |

### accessories

#### Magazine

## Cable marker - UC-WMTB (44X15) YE - 0828379

accessories

P1 UC-MAG 6 - 5146121



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>