

## Cable marker label - US-WML 14 (25X19) - 0800473

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable marker label, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Adhesive, Cable diameter: ≤14 mm, Lettering field: 25 x 19 mm

The figure shows a similar product

### Product Features

- The cable marker labels do not increase the cross section of the cable, allowing the cable to be subsequently drawn through cable ducts, for example
- High-quality labeling image created by thermal transfer printing
- Quick and easy handling
- Resistant to solvents
- The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- US-WML ... cable marker labels consist of a labeling field and a transparent protective foil

### Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356607056

### Technical data

#### Dimensions

<b>Length (b)</b>	25.4 mm
<b>Width (a)</b>	19 mm

#### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-50 °C ... 110 °C

#### General

<b>Color</b>	white
<b>Base element material</b>	Vinyl film
<b>Components</b>	Silicone-free
<b>Material</b>	PVC
<b>Number of individual labels</b>	8
<b>Number of individual labels per row</b>	4
<b>RoHS compliant</b>	Yes
<b>Adhesive</b>	Acrylic
<b>Printability</b>	Thermal transfer

## Cable marker label - US-WML 14 (25X19) - 0800473

### Technical data

#### General

Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Burning behaviour	self-extinguishing
Foil strength	0.06 mm

### classifications

#### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

### accessories

#### Magazine

## Cable marker label - US-WML 14 (25X19) - 0800473

accessories

THERMOMARK CARD-US-MAG1 - 5146451



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>