



Einhell

RED

RG-DP 1135 N Dirt Water Pump

Art.-No. 41.707.00

Features

- Integrated lifting eye (1)
- Carrying handle (2)
- Integrated cable reel (3)
- Continuously height adjustable float switch (4)
- Universal plug approx. 47.8 mm (G 1 ½) female thread (5)
- Impurities up to 35 mm are handled
- Floating ring seal
- Automatic and manual operation
- Hose connection on the upper side
- ECO Power: more flow rate, less power consumption

Technical Data

- Mains: 230 V ~ 50 Hz
- Power: 790 W
- Delivery capacity max.: 20,000 l/h
- Delivery height max.: 9 m
- Immersion depth max.: 8 m
- Universal plug: approx. 47.8 mm (G 1 ½) male thread
- Water temperature max.: 35 °C
- Main cable length: 10 m
- Foreign particles size: Ø 35 mm
- Product weight: 7.4 kg

Logistic Data

- Net weight: 7.5 kg
- Gross weight: 8.4 kg
- Packaging: 270 x 200 x 420 mm
- Bar code: 4006825 572322
- Sales unit: 1 pc

