

Cable marker - UC-WMT (10X4) - 0819372

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable marker, Sheet, white, Unlabeled, Can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Insert, Cable diameter: 0.6-7 mm, Lettering field: 10 x 4 mm

Product Features

- ✓ The UC-WMT ... UniCard labeling range includes markers for conductor marking with marking collars from the PATG/PATO ... system
- ✓ To simplify mounting, the insert labels are arranged on UniCard sheets so that they can be separated branch by branch
- ✓ Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- ✓ Labeled insert strips are simply inserted into the collars. This protects the marking against dirt.
- ✓ The format automatically ensures printing with a high degree of positioning accuracy
- ✓ The sheets provide space for including function texts

Key commercial data

package_quantity	10
GTIN	4046356152242

Technical data

Dimensions

Width (a)	10 mm
------------------	-------

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C

General

Color	white
Base element material	PA
Components	free from silicone and halogen
Inflammability class according to UL 94	V2
Material	PA
Number of individual labels	48
Number of individual labels per row	8
Printability	Inkjet printing
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02

Cable marker - UC-WMT (10X4) - 0819372

Technical data

General

Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Magazine

Cable marker - UC-WMT (10X4) - 0819372

accessories

P1 UC-MAG 4 - 5146105



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>