

Surge protection device - LIT 2X1-24 - 2804636

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Surge protection in one-piece 6.2 mm wide DIN rail module for two conductors with common reference potential.

Product Features

- ✓ Can be used in binary, analog, and intrinsically safe circuits
- ✓ Protection of up to four signal wires over a design width of 6.2 mm



Key commercial data

package_quantity	10
GTIN	4046356428316

Technical data

Dimensions

Height	93 mm
Width	6.2 mm
Depth	102.5 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Degree of protection	IP20

General

Housing material	PBT
Inflammability class according to UL 94	V0
Color	black
Standards for air and creepage distances	IEC 60664-1
Mounting type	DIN rail: 35 mm
Design	Rail-mountable module, one-piece
Direction of action	Line-Earth Ground

Protective circuit

IEC test classification	C1
-------------------------	----

Surge protection device - LIT 2X1-24 - 2804636

Technical data

Protective circuit

IEC test classification	C2
IEC test classification	C3
IEC test classification	D1
Nominal voltage U_N	24 V DC
Maximum continuous operating voltage U_C	25 V AC
Maximum continuous operating voltage U_C	36 V DC
Nominal current I_N	350 mA (40°C)
Operating effective current I_C at U_C	$\leq 2 \mu A$
Residual current I_{PE}	$\leq 4 \mu A$
Nominal discharge current I_n (8/20) μs (Core-Earth)	5 kA
Nominal discharge current I_n (8/20) μs (Core-Earth)	10 kA ((Total))
Total surge current (8/20) μs	20 kA
Total surge current (10/350) μs	1 kA
Max. discharge current I_{max} (8/20) μs maximum (Core-Earth)	10 kA
Max. discharge current I_{max} (8/20) μs maximum (Core-Earth)	20 kA ((Total))
Nominal pulse current I_{an} (10/1000) μs (Core-Earth)	50 A
Nominal pulse current I_{an} (10/1000) μs (Core-Earth)	100 A ((Total))
Impulse discharge current (10/350) μs , peak value I_{imp}	500 A
Output voltage limitation at 1 kV/ μs (Core-Earth) spike	$\leq 60 V$
Residual voltage at I_n , (conductor-ground)	$\leq 50 V$
Residual voltage with I_{an} (10/1000) μs (conductor-ground)	$\leq 60 V$
Voltage protection level U_P (Core-Earth)	$\leq 60 V$ (C1 - 500 V / 250 A)
Voltage protection level U_P (Core-Earth)	$\leq 95 V$ (C2 - 10 kV / 5 kA)
Voltage protection level U_P (Core-Earth)	$\leq 60 V$ (C3 - 10 A)
Response time t_A (Core-Earth)	$\leq 1 ns$
Input attenuation a_E , asym.	typ. 0.3 dB (1 MHz / 50 Ω)
Input attenuation a_E , asym.	typ. 0.2 dB (350 kHz / 150 Ω)
Cut-off frequency f_g (3 dB), asym. (PE) in 50 Ohm system	typ. 6 MHz
Cut-off frequency f_g (3 dB), asym. (PE) in 150 Ohm system	typ. 2 MHz
Capacity	$\leq 1.3 nF$ (per channel)
Resistance in series	3.3 Ω 20 %
Max. required back-up fuse	315 mA
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C2 (10 kV/5 kA)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C3 (25 A)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	D1 (500 A)
Alternating current carrying capacity in acc. with IEC 61643-21 (Core-Earth)	5 A - 1 s

Connection data

Connection method	Screw connection
Connection type IN	Screw terminal blocks

Surge protection device - LIT 2X1-24 - 2804636

Technical data

Connection data

Connection type OUT	Screw terminal blocks
Screw thread	M3
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	12

Connection, equipotential bonding

Connection method	DIN rail NS35
-------------------	---------------

Standards and Regulations

Standards/regulations	IEC 61643-21
Standards/regulations	DIN EN 61643-21

classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000943

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

approvals

UL Listed / GL /

Surge protection device - LIT 2X1-24 - 2804636

approvals

Approval details

UL Listed 

GL

accessories

Terminal marking

UC-TM 6 - 0818085



UC-TM 6 OG - 0818328



UC-TM 6 YE - 0818331



UC-TM 6 BU - 0818344



Surge protection device - LIT 2X1-24 - 2804636

accessories

UC-TM 6 RD - 0818357




UC-TM 6 GN - 0818360




Drawings

Dimensioned drawing



Surge protection device - LIT 2X1-24 - 2804636

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>