

## Insert strip - PABL 15X4 - 0808260

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Insert strip, Sheet, white, Unlabeled, Can be labeled with: Office printing systems, Plotter, Perforated, Mounting type: Insert, Cable diameter: 0.6-50 mm, Lettering field: 15 x 4 mm

### Product Features

- ☒ PABL ... sheets are available for labeling with a laser printer
- ☒ Can be printed with CMS-P1-PLOTTER and office printers

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 10            |
| GTIN             | 4017918171544 |

### Technical data

#### Dimensions

|           |       |
|-----------|-------|
| Width (a) | 15 mm |
|-----------|-------|

#### Ambient conditions

|                                 |                                |
|---------------------------------|--------------------------------|
| Wipe resistance                 | DIN EN 61010-1 (VDE 0411-1)    |
| Ambient temperature (operation) | -40 °C ... 100 °C              |
| Recommended storage conditions  | 23 °C / 50 % relative humidity |

#### General

|                                                                     |                                                 |
|---------------------------------------------------------------------|-------------------------------------------------|
| Note                                                                | Print image may vary depending on laser printer |
| Color                                                               | white                                           |
| Components                                                          | free from silicone and halogen                  |
| Inflammability class according to UL 94                             | V0                                              |
| Material                                                            | Polyester                                       |
| Number of individual labels                                         | 360                                             |
| Number of individual labels per row                                 | 12                                              |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                            |
| Result                                                              | Test passed                                     |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03                    |
| Test duration                                                       | 96 h                                            |
| Wipe resistance test result                                         | Test passed                                     |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02                       |
| Salt spray testing result                                           | Test passed                                     |

## Insert strip - PABL 15X4 - 0808260

### Technical data

#### General

|                                                                     |                   |
|---------------------------------------------------------------------|-------------------|
| <b>Alternating condensation climate with SO2 test specification</b> | DIN 50018:1997-06 |
| <b>Climate level</b>                                                | KFW 1.0 S         |
| <b>Cycles</b>                                                       | 2                 |
| <b>Condensation test result</b>                                     | Test passed       |
| <b>Foil strength</b>                                                | 135 µm            |

### classifications

#### eCl@ss

|                   |          |
|-------------------|----------|
| <b>eCl@ss 4.0</b> | 24190219 |
| <b>eCl@ss 4.1</b> | 24190219 |
| <b>eCl@ss 5.0</b> | 27149103 |
| <b>eCl@ss 5.1</b> | 27141137 |
| <b>eCl@ss 6.0</b> | 27141137 |
| <b>eCl@ss 7.0</b> | 27141137 |
| <b>eCl@ss 8.0</b> | 27141137 |

#### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 2.0</b> | EC000761 |
| <b>ETIM 3.0</b> | EC000761 |
| <b>ETIM 4.0</b> | EC001530 |
| <b>ETIM 5.0</b> | EC001530 |

#### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211811 |
| <b>UNSPSC 7.0901</b> | 39121410 |
| <b>UNSPSC 11</b>     | 39121410 |
| <b>UNSPSC 12.01</b>  | 39121410 |
| <b>UNSPSC 13.2</b>   | 39121410 |

### Drawings