

Surge protection connector - CT 10-2PE/FS-24 - 2807955

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



LSA-PLUS plug (COMTRAB CT 10) with surge voltage coarse and fine protection for 10 floating signal circuits. Nominal voltage: 24 V DC/AC version: 10 double wires

Product Features

- ✓ For use with CT-TERMIBLOCK and with LSA-PLUS and LSA-PROFIL disconnect and control strips
- ✓ Multi-position, plug-in modular design
- ✓ Applications include systems with higher signal voltages
- ✓ Protection modules must be inserted in the correct direction
- ✓ Combined protective circuits



Key commercial data

package_quantity	1
GTIN	4017918104740

Technical data

Dimensions

Height	22 mm
Width	111 mm
Depth	68.5 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 75 °C
Degree of protection	IP20

General

Housing material	PBT
Inflammability class according to UL 94	V0
Color	black
Standards for air and creepage distances	VDE 0110-1
Standards for air and creepage distances	IEC 60664-1
Mounting type	On CT-TERMIBLOCK and LSA-PLUS disconnect strip
Design	LSA-PLUS module
Direction of action	Line-Line & Line-Earth Ground

Surge protection connector - CT 10-2PE/FS-24 - 2807955

Technical data

General

Arrester can be tested with CHECKMASTER from software version:	From SW rev. 1.00
--	-------------------

Protective circuit

IEC test classification	C1
IEC test classification	C2
IEC test classification	C3
IEC test classification	D1
Nominal voltage U_N	24 V DC
Maximum continuous operating voltage U_C	40 V DC
Maximum continuous operating voltage U_C	28 V AC
Maximum continuous voltage U_C (wire-wire)	40 V DC
Nominal current I_N	1.5 A (75 °C)
Operating effective current I_C at U_C	$\leq 5 \mu A$ (a-b)
Residual current I_{PE}	$\leq 1 \mu A$ (per path)
Nominal discharge current I_n (8/20) μs (Core-Core)	119 A (25 °C)
Nominal discharge current I_n (8/20) μs (Core-Earth)	5 kA
Total surge current (8/20) μs	10 kA
Max. discharge current I_{max} (8/20) μs maximum (Core-Core)	119 A (25 °C)
Max. discharge current I_{max} (8/20) μs maximum (Core-Earth)	5 kA
Nominal pulse current I_{an} (10/1000) μs (Core-Core)	23 A (25 °C)
Output voltage limitation at 1 kV/ μs (Core-Core) spike	$\leq 70 V$
Output voltage limitation at 1 kV/ μs (Core-Earth) spike	$\leq 650 V$
Output voltage limitation at 1 kV/ μs (Core-Core) static	$\leq 60 V$
Output voltage limitation at 1 kV/ μs (Core-Earth) static	$\leq 650 V$
Residual voltage at I_n , (conductor-conductor)	$\leq 85 V$
Residual voltage with I_{an} (10/1000) μs (conductor-conductor)	$\leq 65 V$
Response time t_A (Core-Core)	$\leq 1 ns$
Response time t_A (Core-Earth)	$\leq 100 ns$
Input attenuation a_E , sym.	0.1 dB (Typ. up to 2 MHz / 50 Ω)
Input attenuation a_E , sym.	0.1 dB (Typ. up to 1 MHz / 150 Ω)
Input attenuation a_E , sym.	0.1 dB (Typ. up to 400 kHz / 600 Ω)
Cut-off frequency f_g (3 dB), sym. in 50 Ohm system	10 MHz (typ.)
Cut-off frequency f_g (3 dB), sym. in 150 Ohm system	4 MHz (typ.)
Cut-off frequency f_g (3 dB), sym. in 600 Ohm system	1 MHz (typ.)
Capacity (Core-Core)	1.1 nF ($f=1 MHz / V_R=0 V$)
Capacity (Core-Earth)	1 pF
Message: Surge protection fault	None
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C1 (1 kV / 500 A)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C2 (10 kV/5 kA)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	C3 (100 A)
Surge carrying capacity in acc. with IEC 61643-21 (Core-Earth)	D1 (2.5 kA)

Surge protection connector - CT 10-2PE/FS-24 - 2807955

Technical data

Connection data

Connection method	can be plugged into COMTRAB-TERMIBLOCK and LSA-PLUS disconnect and switching strips
Connection type IN	COMTRAB plug-in system
Connection type OUT	COMTRAB plug-in system

Standards and Regulations

Standards/regulations	IEC 61643-21
------------------------------	--------------

classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27130801
eCl@ss 5.0	27130801
eCl@ss 5.1	27130801
eCl@ss 6.0	27130807
eCl@ss 7.0	27130807
eCl@ss 8.0	27130807

ETIM

ETIM 2.0	EC000943
ETIM 3.0	EC000943
ETIM 4.0	EC000943
ETIM 5.0	EC000943

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620

approvals

GOST /

Approval details

GOST 

Surge protection connector - CT 10-2PE/FS-24 - 2807955

accessories


Screw termination block

CT-TERMIBLOCK 10 DA - 0441711




Drawings

Dimensioned drawing



Surge protection connector - CT 10-2PE/FS-24 - 2807955

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>