



Einhell

EH 3000 Electric Heater

Art.-No. 23.382.60

Whether to the fast heat of workshop, small stockrooms, party tents or for draining of singular rooms – owing to the high heating power of 3.0 kW always sufficiently warmth is available. After switch off the unit the fan run continuing for some minutes to cool down the hot heating elements.

Features

- Stable feet with integrated handle (1)
- Zinc-coated housing back board
- Air discharge grid made of powder coated wire mesh (2)
- High-quality rubber power line
- Powerful axial blow fan with aluminium blower wheel (3)
- 2 special heating elements made of metal (4)
- Switch with 2 heating levels (1,500/3,000 W) and fan operation (5)
- Continuously adjustable thermostat regulation (6)
- Fan run continuing after switch off to cool down the heating elements
- Overheating protection
- Splash guard

Technical Data

- Mains: 230 V ~ 50Hz
- Heating Power: 3,000 Watt
- Battery backup: 16 A
- Protection category : IP24
- Unit dimensions: 295 x 250 x 430 mm
- Product weight: 5.7 kg

Logisitic Data

- Net weight: 5.7 kg
- Gross weight: 7.0 kg
- Packing dimensions: 320 x 320 x 465 mm
- Bar code: 4006825 548242
- Sales Unit: 1 pc

