



Type Number..... 6025
Designation IEC..... CR 2025
System..... Li-Manganese dioxide/
 Organic Electrolyte

UL Recognition..... MH 13654 (N)
Nominal Voltage..... 3 V
Typical Capacity C..... 157 mAh
 Load 10 kOhm, at 20°C down to 2 V

Weight (approx.)..... 2,5 g
Volume..... 0,75 ccm

Temperature Ranges min max.
Storage..... -55°C 70°C
Discharge..... -20°C 70°C

Dimensions min max.
Diameter (A) 19,7 20,0
Height (B)..... 2,2 2,5
Shoulder Diameter [E] 18,3
Shoulder Height [C] 0,2

Segment..... Photo

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0V
Continuous 24h/d, 7d/w	15000 Ω	Time: Capacity: Energy:	810 h 157 mAh 435 mWh

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries

All Data contained herein is for single cells
 For battery applications, performance data may vary from single cell data, depending on specific battery configuration