

## Installation level terminal block - UTI 2,5-L/N - 3076035

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Installation level terminal block, Screw connection, Cross section: 0.2 mm<sup>2</sup> - 4 mm<sup>2</sup>, AWG: 24 - 12, Width: 5.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

### Product Features

- ✔ The installation terminal block features a particularly low-profile design and is suitable for wiring in flat installation distributors
- ✔ The asymmetrical arrangement of the terminal blocks on the DIN rail enables the neutral busbar to be routed past the terminal blocks

### Key commercial data

package_quantity	50
GTIN	4046356643986

### Technical data

#### General

Note	Assembly instructions:For secure fastening of the neutral busbar, supports must be set at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips.
Number of levels	3
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

#### General

Maximum load current	30 A (with 4 mm <sup>2</sup> conductor cross section and 3-pos. terminal block)
Maximum load current	24 A (with 2.5 mm <sup>2</sup> conductor cross section)
Current carrying capacity of the neutral busbar	140 A
Rated surge voltage	4 kV
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal current I <sub>N</sub>	24 A (with 4 mm <sup>2</sup> conductor cross section)
Nominal voltage U <sub>N</sub>	400 V (phase conductor/phase conductor)
Nominal voltage U <sub>N</sub>	(phase conductor/PE)

# Installation level terminal block - UTI 2,5-L/N - 3076035

## Technical data

### General

Nominal voltage $U_N$	250 V (phase conductor/N)
Open side panel	ja
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed
Finger protection	guaranteed
Surge voltage test setpoint	7.3 kV
Result of surge voltage test	Test failed
Power frequency withstand voltage setpoint	1.89 kV
Result of power-frequency withstand voltage test	Test performed
Checking the mechanical stability of terminal points (5 x conductor connection)	Test passed
Bending test rotation speed	10 rpm
Bending test turns	135
Bending test conductor cross section/weight	0.2 mm <sup>2</sup> / 0.2 kg
Bending test conductor cross section/weight	2.5 mm <sup>2</sup> / 0.7 kg
Bending test conductor cross section/weight	4 mm <sup>2</sup> / 0.9 kg
Result of bending test	Test passed
Conductor cross section tensile test	0.2 mm <sup>2</sup>
Tractive force setpoint	10 N
Conductor cross section tensile test	2.5 mm <sup>2</sup>
Tractive force setpoint	50 N
Conductor cross section tensile test	4 mm <sup>2</sup>
Tractive force setpoint	60 N
Tensile test result	Test passed
Tight fit on carrier	NS 35
Setpoint	1 N
Result of tight fit test	Test passed
Requirements, voltage drop	≤ 3.2 mV
Result of voltage drop test	Test passed
Temperature-rise test	Test passed
Conductor cross section short circuit testing	2.5 mm <sup>2</sup>
Short-time current	0.3 kA
Conductor cross section short circuit testing	4 mm <sup>2</sup>
Short-time current	0.48 kA
Short circuit stability result	Test passed
Proof of thermal characteristics (needle flame) effective duration	30 s
Result of thermal test	Test passed
Test specification, oscillation, broadband noise	DIN EN 50155 (VDE 0115-200):2008-03
Test spectrum	Service life test category 2, bogie mounted
Test frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$
ASD level	6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz

# Installation level terminal block - UTI 2,5-L/N - 3076035

## Technical data

### General

Acceleration	3.12 g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Oscillation, broadband noise test result	Test passed
Test specification, shock test	DIN EN 50155 (VDE 0115-200):2008-03
Shock form	Half-sine
Acceleration	30 g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Shock test result	Test passed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C

### Dimensions

Width	5.2 mm
Length	93.5 mm
Height NS 35/7,5	51.5 mm

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	4 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm <sup>2</sup>
2 conductors with same cross section, solid min.	0.2 mm <sup>2</sup>
2 conductors with same cross section, solid max.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded min.	0.2 mm <sup>2</sup>
2 conductors with same cross section, stranded max.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	0.75 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm <sup>2</sup>

# Installation level terminal block - UTI 2,5-L/N - 3076035

## Technical data

### Connection data

<b>2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.</b>	0.75 mm <sup>2</sup>
<b>Connection method</b>	Screw connection
<b>Stripping length</b>	9 mm
<b>Internal cylindrical gage</b>	A3
<b>Screw thread</b>	M3
<b>Tightening torque, min</b>	0.5 Nm
<b>Tightening torque max</b>	0.6 Nm

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27141120
<b>eCl@ss 4.1</b>	27141120
<b>eCl@ss 5.0</b>	27141120
<b>eCl@ss 5.1</b>	27141120
<b>eCl@ss 6.0</b>	27141120
<b>eCl@ss 7.0</b>	27141120
<b>eCl@ss 8.0</b>	27141120

### ETIM

<b>ETIM 3.0</b>	EC000897
<b>ETIM 4.0</b>	EC001329
<b>ETIM 5.0</b>	EC001329

### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410

## accessories

### Screwdriver tools

SZS 0,6X3,5 - 1205053



## Installation level terminal block - UTI 2,5-L/N - 3076035

accessories

### Neutral conductor rail

NLS-CU 3/10 SN 1000MM - 0402174



---

### Warning label printed

WS UT 2,5 - 3047923



---

### Installation terminal block

AKG 16 BU - 0423014



AKG 35 BU - 0424013



---

### Support

AB-UTI/3 - 3076038



# Installation level terminal block - UTI 2,5-L/N - 3076035

accessories

---

## End cover

D-UTI/3 - 3076036



DP PS-5 - 3036725



## Partition plate

ATP-PTI/3 - 3213990



## Bridge

FBS 2-5 - 3030161



FBS 3-5 - 3030174



## Installation level terminal block - UTI 2,5-L/N - 3076035

### accessories

FBS 4-5 - 3030187



FBS 5-5 - 3030190



FBS 10-5 - 3030213



FBS 20-5 - 3030226



FBS 50-5 - 3038930



### Mounting rail

## Installation level terminal block - UTI 2,5-L/N - 3076035

### accessories

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421





## Installation level terminal block - UTI 2,5-L/N - 3076035

### accessories

---

NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



## Installation level terminal block - UTI 2,5-L/N - 3076035

### accessories

NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



## Installation level terminal block - UTI 2,5-L/N - 3076035

### accessories

---

NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



### Terminal marking

---

ZB 5 :UNBEDRUCKT - 1050004



UC-TM 5 - 0818108



UCT-TM 5 - 0828734



## Installation level terminal block - UTI 2,5-L/N - 3076035

### accessories

ZBF 5:UNBEDRUCKT - 0808642



---

UC-TMF 5 - 0818153



---

UCT-TMF 5 - 0828744



---

### Labeled terminal marker

ZB 5 CUS - 0824962



---

UC-TM 5 CUS - 0824581



## Installation level terminal block - UTI 2,5-L/N - 3076035

### accessories

UCT-TM 5 CUS - 0829595



ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



UCT-TMF 5 CUS - 0829658



### **Test plug terminal block**

MPS-MT - 0201744



## Installation level terminal block - UTI 2,5-L/N - 3076035

### accessories

PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



PAI-4-FIX-5/6 BK - 3035980



## Installation level terminal block - UTI 2,5-L/N - 3076035

### accessories

---

PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



PS-5 - 3030983



PS-5/2,3MM RD - 3038723



### Insulating sleeve

## Installation level terminal block - UTI 2,5-L/N - 3076035

### accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728





# Installation level terminal block - UTI 2,5-L/N - 3076035

## accessories

---

MPS-IH BK - 0201731



## Planning and marking software

---

CLIP-PROJECT ADVANCED - 5146040



CLIP-PROJECT PROFESSIONAL - 5146053



## End block

---

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



# Installation level terminal block - UTI 2,5-L/N - 3076035

accessories

E/NS 35 N - 0800886



---

## Drawings

Circuit diagram

