

## Pick-off terminal block - AGK 10-PTPOWER BU - 3260148

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Pick-off terminal block, Connection method: Push-in connection, Cross section: 0.5 mm<sup>2</sup> - 16 mm<sup>2</sup>, AWG: 20 - 6, Width: 18.5 mm, Height: 34.7 mm, Color: blue, Mounting type: On base element

### Product Features

- The fully insulated, optional use pick-off terminal block enables voltage pick-off
- Large-surface marking
- Pick-off terminal block, for snapping into the lateral guide

### Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356779081

### Technical data

#### General

<b>Number of levels</b>	1
<b>Number of connections</b>	2
<b>Color</b>	blue
<b>Insulating material</b>	PA
<b>Inflammability class according to UL 94</b>	V0

#### General

<b>Rated surge voltage</b>	8 kV
<b>Pollution degree</b>	3
<b>Surge voltage category</b>	III
<b>Insulating material group</b>	I
<b>Nominal current I<sub>N</sub></b>	57 A
<b>Nominal voltage U<sub>N</sub></b>	1500 V
<b>Open side panel</b>	nein

#### Dimensions

<b>Width</b>	18.5 mm
<b>Length</b>	35 mm
<b>Height</b>	34.7 mm

#### Connection data

<b>Conductor cross section solid min.</b>	0.5 mm <sup>2</sup>
---	---------------------

## Pick-off terminal block - AGK 10-PTPOWER BU - 3260148

### Technical data

#### Connection data

Conductor cross section solid max.	16 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	6
Conductor cross section stranded min.	0.5 mm <sup>2</sup>
Conductor cross section stranded max.	10 mm <sup>2</sup>
Min. AWG conductor cross section, stranded	20
Max. AWG conductor cross section, stranded	8
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve max.	10 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve max.	10 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	2.5 mm <sup>2</sup>
Connection method	Push-in connection
Stripping length	18 mm
Internal cylindrical gage	A6

### classifications

#### eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141148
eCl@ss 7.0	27141148
eCl@ss 8.0	27141148

#### ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC002021

#### UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

# Pick-off terminal block - AGK 10-PTPOWER BU - 3260148


approvals

---

GOST /

---

Approval details



accessories

**Screwdriver tools**

SZF 1-0,6X3,5 - 1204517



---

**Terminal marking**

ZB 10:UNBEDRUCKT - 1053001



---

UC-TM 10 - 0818069



---

UCT-TM 10 - 0829142



## Pick-off terminal block - AGK 10-PTPOWER BU - 3260148

accessories

ZBF10:UNBEDRUCKT - 0809997



---

UC-TMF 10 - 0818124



---

UCT-TMF 10 - 0829204



---

TMT (EX9,5)R - 0828295



---

**Labeled terminal marker**

ZB 10 CUS - 0824941



## Pick-off terminal block - AGK 10-PTPOWER BU - 3260148

accessories

UC-TM 10 CUS - 0824605



UCT-TM 10 CUS - 0829623



ZBF10 CUS - 0825031



UC-TMF 10 CUS - 0824662



UCT-TMF 10 CUS - 0829679



**Test plug terminal block**

## Pick-off terminal block - AGK 10-PTPOWER BU - 3260148

accessories

MPS-MT - 0201744



---

### Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



## Pick-off terminal block - AGK 10-PTPOWER BU - 3260148

### accessories

MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>