


# NTC Thermistor : TTS Series



## Epoxy Bead Type for Temperature Sensing/Compensation

### ■ Features


1. RoHS compliant
2. Halogen-Free (HF) series are available
3. Body size:  $\Phi 1.8\text{mm}$ ,  $\Phi 2.6\text{mm}$
4. Radial lead resin coated
5. Long leads for easy sensor placement
6. Operating temperature range:  $-40^{\circ}\text{C} \sim +100^{\circ}\text{C}$
7. Wide resistance range
8. Agency recognition: UL / cUL



### ■ Recommended Applications


1. Home appliances
2. Computers
3. Battery packs
4. Thermometers

### ■ Part Number Code



### ■ Structure and Dimensions


#### R Type



(Unit: mm)

Series	Dmax.	Amax.	d	L	I
TTS1	1.8	6.0	0.30 $\pm$ 0.02	70 $\pm$ 5	2 $\pm$ 0.5
TTS2	2.6	6.0			

#### G Type



(Unit: mm)


Series	Dmax.	Amax.	d	L
TTS1	1.8	6.0	0.30 $\pm$ 0.02	70 $\pm$ 5
TTS2	2.6	6.0		

# NTC Thermistor : TTS Series

Epoxy Bead Type for Temperature Sensing/Compensation



## T Type



(Unit: mm)

Series	Dmax.	Amax.	d	L	l
TTS1	1.8	6.0	0.30±0.02	70±5	2±0.5

## Electrical Characteristics

Part No.	Zero Power Resistance at 25°C	Tolerance of R <sub>25</sub>	B Value	Tolerance of B value	Max. Power Dissipation at 25°C	Dissipation Factor	Thermal Time Constant	Operating Temperature Range	Safety Approvals								
	R <sub>25</sub> (KΩ)								(±%)	(K)	(±%)	P <sub>max</sub> (mW)	δ(mW/°C)	τ (Sec.)	T <sub>L</sub> -T <sub>U</sub> (°C)	UL	cUL
TTS1A103□34D*	10	1, 2, 3, 5	25/85	1, 2, 3	45	≥ 1	≤ 10	-40 ~ +100	√	√							
TTS1A103□395*	10								√	√							
TTS1A103□39H*	10								√	√							
TTS1A103□426*	10								√	√							
TTS1A223□370*	22								√	√							
TTS1A333□405*	33								√	√							
TTS1A104□436*	100								√	√							
TTS1B104□410*	100								√	√							
TTS2A502□39H*	5								1, 2, 3, 5	25/85	1, 2, 3	45	≥ 1	≤ 10	-40 ~ +100	√	√
TTS2A103□34D*	10															√	√
TTS2A103□396*	10	√	√														
TTS2A103□39H*	10	√	√														
TTS2A203□34D*	20	√	√														
TTS2A104□436*	100	√	√														
TTS2B102□392*	1	25/50	1, 2, 3	2, 3	45	≥ 1	≤ 10	-40 ~ +100								√	√
TTS2B502□39D*	5															√	√
TTS2B104□410*	100															√	√
TTS2B104□419*	100															√	√
TTS2B474□439*	470								√	√							
									√	√							

Note 1: □ = Tolerance of R<sub>25</sub>

\* = Tolerance of B value

Note 2: UL/cUL File No: E138827


Note 3: Special specifications are available upon request.

# NTC Thermistor : TTS Series

Epoxy Bead Type for Temperature Sensing/Compensation



## Max. Power Dissipation Derating Curve



$T_U$  : Maximum operating temperature (°C)

$T_L$  : Minimum operating temperature (°C)



For example:

Ambient temperature( $T_a$ ) = 55°C

Maximum operating temperature( $T_U$ ) = 100°C

$$P_{Ta} = (T_U - T_a) / (T_U - 25) \times P_{max} = 60\% P_{max}$$

## R-T Characteristic Curves




# NTC Thermistor : TTS Series

Epoxy Bead Type for Temperature Sensing/Compensation



## ■ Soldering Recommendation

### ● Wave Soldering Profile



### ● Recommended Reworking Conditions With Soldering Iron

Item	Conditions
Temperature of Soldering Iron-tip	$360^\circ\text{C}$ (max.)
Soldering Time	3 sec. (max.)
Distance from Thermistor	10 mm (min.)

# NTC Thermistor : TTS Series



## Epoxy Bead Type for Temperature Sensing/Compensation

### ■ Reliability

Item	Standard	Test conditions / Methods	Specifications															
Tensile Strength of Terminations	IEC 60068-2-21	Gradually apply the specified force and keep the unit fixed for 10±1 sec. <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Terminal diameter (mm)</th> <th>Force (Kg)</th> </tr> </thead> <tbody> <tr> <td><math>d \leq 0.25</math></td> <td>0.10</td> </tr> <tr> <td><math>0.25 &lt; d \leq 0.3</math></td> <td>0.25</td> </tr> <tr> <td><math>0.3 &lt; d \leq 0.5</math></td> <td>0.5</td> </tr> </tbody> </table>	Terminal diameter (mm)	Force (Kg)	$d \leq 0.25$	0.10	$0.25 < d \leq 0.3$	0.25	$0.3 < d \leq 0.5$	0.5	No visible damage							
Terminal diameter (mm)	Force (Kg)																	
$d \leq 0.25$	0.10																	
$0.25 < d \leq 0.3$	0.25																	
$0.3 < d \leq 0.5$	0.5																	
Bending Strength of Terminations	IEC 60068-2-21	Hold specimen and apply the force specified below to each lead. Bend the specimen to 90°, and then return to the original position. Repeat the procedure in the opposite direction. <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Terminal diameter (mm)</th> <th>Force (Kg)</th> </tr> </thead> <tbody> <tr> <td><math>d \leq 0.25</math></td> <td>0.05</td> </tr> <tr> <td><math>0.25 &lt; d \leq 0.3</math></td> <td>0.125</td> </tr> <tr> <td><math>0.3 &lt; d \leq 0.5</math></td> <td>0.25</td> </tr> </tbody> </table>	Terminal diameter (mm)	Force (Kg)	$d \leq 0.25$	0.05	$0.25 < d \leq 0.3$	0.125	$0.3 < d \leq 0.5$	0.25	No visible damage							
Terminal diameter (mm)	Force (Kg)																	
$d \leq 0.25$	0.05																	
$0.25 < d \leq 0.3$	0.125																	
$0.3 < d \leq 0.5$	0.25																	
Solderability	IEC 60068-2-20	245 ± 3°C, 3 ± 0.3 sec	At least 95% of terminal electrode is covered by new solder															
Resistance to Soldering Heat	IEC 60068-2-20	260 ± 3°C, 10 ± 1 sec.	No visible damage   $\Delta R_{25}/R_{25}$   ≤ 3 %															
High Temperature Storage	IEC 60068-2-2	100 ± 5°C, 1000 ± 24 hrs	No visible damage   $\Delta R_{25}/R_{25}$   ≤ 5 %															
Damp Heat, Steady State	IEC 60068-2-78	40 ± 2°C, 90~95% RH, 1000 ± 24 hrs	No visible damage   $\Delta R_{25}/R_{25}$   ≤ 3 %															
Rapid Change of Temperature	IEC 60068-2-14	The conditions shown below shall be repeated 5 cycles. <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th>Step</th> <th>Temperature (°C)</th> <th>Period (minutes)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-40 ± 5</td> <td>30 ± 3</td> </tr> <tr> <td>2</td> <td>Room temperature</td> <td>5 ± 3</td> </tr> <tr> <td>3</td> <td>100 ± 5</td> <td>30 ± 3</td> </tr> <tr> <td>4</td> <td>Room temperature</td> <td>5 ± 3</td> </tr> </tbody> </table>	Step	Temperature (°C)	Period (minutes)	1	-40 ± 5	30 ± 3	2	Room temperature	5 ± 3	3	100 ± 5	30 ± 3	4	Room temperature	5 ± 3	No visible damage   $\Delta R_{25}/R_{25}$   ≤ 3 %
Step	Temperature (°C)	Period (minutes)																
1	-40 ± 5	30 ± 3																
2	Room temperature	5 ± 3																
3	100 ± 5	30 ± 3																
4	Room temperature	5 ± 3																
Max. Power Dissipation	IEC 60539-1	25 ± 5°C, Pmax., 1000 ± 24 hrs	No visible damage   $\Delta R_{25}/R_{25}$   ≤ 5 %															

### ■ Packaging

- Bulk Packing: 500 pcs/bag

### ■ Warehouse Storage Conditions of Products

- Storage Conditions :
  1. Storage Temperature: -10°C~+40°C
  2. Relative Humidity: ≤75%RH
  3. Keep away from corrosive atmosphere and sunlight.
- Period of Storage : 1 year