

Ground modular terminal block - USLKG 35 - 0444019

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ground modular terminal block, Connection method: Screw connection, Cross section: 0.75 mm² - 50 mm², AWG: 18 - 1/0, Width: 15.2 mm, Color: green-yellow, Mounting type: NS 35/7,5, NS 35/15, NS 32



Key commercial data

package_quantity	25
GTIN	4017918002329

Technical data

General

Note	Use an NS 32... or NS 35... copper DIN rail for connection cross sections of 35 mm ² /2 AWG. Use an NS 32... copper DIN rail for connection cross sections > 35 mm ² /2 AWG. When aligning with a feed-through terminal block of the same shape, a cover must be used for insulation voltages > 690 V.
Number of levels	1
Number of connections	2
Color	green-yellow
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	150 A (with 50 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-2
Nominal current I _N	150 A
Open side panel	nein

Dimensions

Width	15.2 mm
Length	50 mm

Ground modular terminal block - USLKG 35 - 0444019

Technical data

Dimensions

Height NS 35/7,5	62 mm
------------------	-------

Connection data

Note	Terminal point
Conductor cross section solid min.	0.75 mm ²
Conductor cross section solid max.	50 mm ²
Conductor cross section AWG/kcmil min.	18
Conductor cross section AWG/kcmil max	1/0
Conductor cross section stranded min.	0.75 mm ²
Conductor cross section stranded max.	35 mm ²
Min. AWG conductor cross section, stranded	18
Max. AWG conductor cross section, stranded	2
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.75 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	35 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.75 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	35 mm ²
2 conductors with same cross section, solid min.	0.75 mm ²
2 conductors with same cross section, solid max.	16 mm ²
2 conductors with same cross section, stranded min.	0.75 mm ²
2 conductors with same cross section, stranded max.	10 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.75 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	10 mm ²
Connection method	Screw connection
Stripping length	15 mm
Screw thread	M6
Tightening torque, min	3.2 Nm
Tightening torque max	3.7 Nm

classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118

Ground modular terminal block - USLKG 35 - 0444019

classifications

eCl@ss

eCl@ss 6.0	27141141
eCl@ss 7.0	27141141
eCl@ss 8.0	27141141

ETIM

ETIM 2.0	EC000901
ETIM 3.0	EC000901
ETIM 4.0	EC000901
ETIM 5.0	EC000901

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

IECEX / ATEX / CSA / UL Recognized / cUL Recognized / GOST / LR / BV / DNV / RS / ABS / PRS / GOST / cULus Recognized / BV /

Approval details

IECEX	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	0.75-50

ATEX 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	0.75-35

CSA 	
Nominal voltage UN	
Nominal current IN	

Ground modular terminal block - USLKG 35 - 0444019

approvals

mm²/AWG/kcmil	18-2

UL Recognized 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	18

cUL Recognized 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	18

GOST 	
---	--

LR

BV

DNV

RS

ABS	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	18

PRS

	
---	--

Ground modular terminal block - USLKG 35 - 0444019

approvals

cULus Recognized  US

accessories

Terminal marking

SBS10:UNBEDRUCKT - 1007248



ZB 10:UNBEDRUCKT - 1053001



UC-TM 10 - 0818069



UCT-TM 10 - 0829142



Mounting rail

Ground modular terminal block - USLKG 35 - 0444019

accessories

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



Ground modular terminal block - USLKG 35 - 0444019

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Ground modular terminal block - USLKG 35 - 0444019

accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



Ground modular terminal block - USLKG 35 - 0444019

accessories

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



Labeled terminal marker

ZB 10 CUS - 0824941



UC-TM 10 CUS - 0824605



Ground modular terminal block - USLKG 35 - 0444019

accessories

UCT-TM 10 CUS - 0829623



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>