

# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Pre-assembled relay modules with push-in connection, consisting of: relay base, power contact relay, plug-in display/suppressor module, and retaining bracket. Input voltage: 230 V AC, 3 N/O contacts

The figure shows the 24 V DC version

## Key commercial data

<b>package_quantity</b>	5
<b>GTIN</b>	4046356731614

## Technical data

### Dimensions

<b>Width</b>	43 mm
<b>Height</b>	111 mm
<b>Depth</b>	90 mm

### Ambient conditions

<b>Ambient temperature (operation)</b>	-40 °C ... 40 °C
<b>Ambient temperature (storage/transport)</b>	-40 °C ... 85 °C

### Coil side

<b>Nominal input voltage <math>U_N</math></b>	230 V AC
<b>Input voltage range in reference to <math>U_N</math></b>	(refer to the diagram)
<b>Nominal input current at <math>U_{IN}</math></b>	14 mA
<b>Typical response time</b>	5 ms ... 25 ms
<b>Typical release time range</b>	5 ms ... 20 ms
<b>Operating voltage display</b>	Yellow LED
<b>Protective circuit</b>	Varistor

### Contact side

<b>Contact type</b>	3 N/O contacts
<b>Contact material</b>	AgNi
<b>Maximum switching voltage</b>	440 V AC
<b>Maximum switching voltage</b>	250 V DC
<b>Minimum switching voltage</b>	10 V (At 24 mA)
<b>Maximum inrush current</b>	50 A (20 ms, N/O contact)
<b>Min. switching current</b>	10 mA (at 24 V)

# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273

## Technical data

### Contact side

Limiting continuous current	8 A (refer to the diagram)
Interrupting rating (ohmic load) max.	216 W (at 24 V DC)
Interrupting rating (ohmic load) max.	480 W (at 48 V DC)
Interrupting rating (ohmic load) max.	600 W (at 60 V DC)
Interrupting rating (ohmic load) max.	660 W (at 110 V DC)
Interrupting rating (ohmic load) max.	183 W (at 220 V DC)
Interrupting rating (ohmic load) max.	2250 VA (for 250 V AC)
Interrupting rating (ohmic load) max.	4000 VA (At 440 V AC)
Switching capacity in acc. with DIN VDE 0660/IEC 60947	1 A (24 V (DC13))
Switching capacity in acc. with DIN VDE 0660/IEC 60947	1.5 A (230 V (AC 15))

### Connection data

Connection method	Push-in connection
Connection name	Input
Connection method	Push-in connection
Conductor cross section solid min.	0.14 mm <sup>2</sup>
Conductor cross section solid max.	1.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.14 mm <sup>2</sup>
Conductor cross section stranded max.	1.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve max.	1.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve max.	1.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	16
Stripping length	8 mm
Connection name	Output
Connection method	Push-in connection
Conductor cross section solid min.	0.14 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.14 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm <sup>2</sup>

# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273

## Technical data

### Connection data

Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Stripping length	10 mm

### General

Test voltage relay winding/relay contact	2.5 kV <sub>rms</sub> (50 Hz, 1 min.)
Test voltage relay contact/relay contact	2.5 kV <sub>rms</sub> (50 Hz, 1 min.)
Operating mode	100% operating factor
Degree of protection	IP20 (Relaissockel)
Degree of protection	RT I (Relais)
Mechanical service life	Approx. 10 <sup>7</sup> cycles
Standards/regulations	DIN EN 50178
Standards/regulations	IEC 62103
Rated insulation voltage	250 V AC
Pollution degree	2
Surge voltage category	III
Mounting position	Any
Assembly instructions	In rows with zero spacing

## classifications

### eCl@ss

eCl@ss 4.0	27371102
eCl@ss 4.1	27371102
eCl@ss 5.0	27371603
eCl@ss 5.1	27371603
eCl@ss 6.0	27371603
eCl@ss 7.0	27371603
eCl@ss 8.0	27371603

### ETIM

ETIM 3.0	EC001456
ETIM 4.0	EC001456
ETIM 5.0	EC001437

### UNSPSC

UNSPSC 6.01	30211917
UNSPSC 7.0901	39121516
UNSPSC 11	39121516
UNSPSC 12.01	39121516
UNSPSC 13.2	39121516

# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273


## approvals

---

CSA /

---

## Approval details



## accessories

### Bridge

FBS 2-6 - 3030336



---

FBS 2-6 BU - 3036932



---

FBS 2-6 GY - 3032237



---

FBS 5-6 - 3030349



## Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273

### accessories

FBS 10-6 - 3030271



FBS 20-6 - 3030365



FBS 50-6 - 3032224



### End block

CLIPFIX 35 - 3022218



### Test plug terminal block

MPS-MT - 0201744



### Insulating sleeve

# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273

## accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273

## accessories

---

MPS-IH BK - 0201731



## Terminal marking

---

ZB 5 :UNBEDRUCKT - 1050004




ZB 15:UNBEDRUCKT - 0811972



## Drawings

# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273

Diagram




Operating voltage range



# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273


Diagram



Interrupting rating

# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273


Diagram



Contact derating

# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273


Diagram



❶ 250 V AC, ohmic load

Electrical service life


Diagram



Service life reduction factor

# Relay Module - RIF-4-RPT-LV-230AC/3X1 - 2903273

Circuit diagram



AC coils

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>