

UNPACKED
completely ready
for installation
comes with
motor and blades

- puristic cylindrical shape
- silent and balanced running
- with light kit on request

25 YEARS
LIMITED MOTOR
WARRANTY

THE ZONIX SN #FP4620SN
housing satin nickel, with reversible blades
cherry (see picture)/walnut

Available on request:
220-240
110-120 V/~60 Hz



Optional housing accessory
Zonix #HA4620CY
(cherry woven)



Optional housing accessory
Zonix #HA4620WA
(walnut woven)



Optional light kit
1 x 13 W*
Zonix #LK4620SN
(Satin nickel)
or #LK 46200B (Oil rubbed bronze)




Optional blade set
Ø 112 cm, Satin nickel,
#B4442SN

Optional reversible blade set
Ø 112 cm, cherry/walnut,
#B4442CWR

Optional blade set
Ø 112 cm, black,
#B4442BL

*The optional luminaire is compatible with bulbs of the energy classes: E - A++.

Dimensions mm



THE ZONIX

No. of blades	3
Power motor (W)	13 - 70
Size Ø (cm/")	137/54
Voltage (V/Hz)	220-240/~50
No. speeds (with W/C)	4
Rotation max (RPM)	150
Weight (kg)	10.0

Installation: 2 screws Ø min. 4.5 mm
separation 70 - 110 mm

Clear and businesslike— remarkably unremarkable

- 3 reversible blades cherry/walnut Ø 137 cm.
- Installation on sloped ceilings (up to 30°).
- 4-speed wall control included.
- Forward/reverse slide switch.
- Whisper-quiet performance by very high quality motors and ball bearings.
- Balanced motor and blades.

Options:

- Opal glass light kit 1x 13 W E27 for ESL.
- Additional blades for Ø 112 cm available.
- Longer downrods for high ceilings available (page 124).
- Opt. controls available (pages 116 - 119).



THE ZONIX OB #FP46200B,
housing oil rubbed bronze, reversible blades
cherry (showing)/walnut

4-speed wall control
included.



Product	Code No.	Housing Finish	Reversible Blade Finish
THE ZONIX SN	FP4620SN	Satin nickel	Cherry/Walnut
THE ZONIX OB	FP46200B	Oil rubbed bronze	Cherry/Walnut