

Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator terminal block, Cross section: 0.2 mm² - 4 mm², AWG: 24 - 12, Connection type: Screw connection, Width: 6.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

Product Features

- This terminal block has 2 feed-through levels and 2 busbar levels
- It is used for programmable or self-monitoring initiators which are additionally controlled via the second feed-through level

Key commercial data

package_quantity	50
GTIN	4017918062262

Technical data

General

Number of levels	4
Number of connections	6
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V2

General

Rated surge voltage	4 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	24 A
Nominal voltage U _N	250 V
Open side panel	nein

Dimensions

Width	6.2 mm
Length	73 mm
Height NS 35/7,5	70 mm
Height NS 35/15	77.5 mm

Connection data

Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

Technical data

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm ²
Cross section with insertion bridge, solid max.	4 mm ²
Cross section with insertion bridge, stranded max.	2.5 mm ²
Connection method	Screw connection
Stripping length	8 mm
Internal cylindrical gage	A3
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141128
eCl@ss 7.0	27141128

Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

classifications

eCl@ss

eCl@ss 8.0	27141128
------------	----------

ETIM

ETIM 2.0	EC000900
ETIM 3.0	EC000900
ETIM 4.0	EC000900
ETIM 5.0	EC000900

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

CSA / UL Recognized / cUL Recognized / cULus Recognized /

Approval details

Nominal voltage UN	300 V
Nominal current IN	15 A
mm ² /AWG/kcmil	28-14


Nominal voltage UN	300 V
Nominal current IN	15 A
mm ² /AWG/kcmil	30-14

Nominal voltage UN	300 V
Nominal current IN	15 A

Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

approvals

mm ² /AWG/kcmil	30-14
----------------------------	-------



accessories

Labeled terminal marker

SK 6,2/3,8:FORTL.ZAHLEN - 0804374



ZB 6 CUS - 0824992



UC-TM 6 CUS - 0824589



UCT-TM 6 CUS - 0829602



Bridge

Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

accessories

FB-150 METER - 0201595



FBI 100- 6 - 0201650



FBI 10- 6 - 0203250



FBI 20- 6 - 0201867



EB 80- DIK BU - 2715940



EB 10- DIK RD - 2716774



Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

accessories

EB 10- DIK BU - 2716680



EB 80- DIK RD - 2715953



EB 10- DIK GY - 2715937



EB 80- DIK WH - 2715788



Terminal marking

SBS 6:UNBEDRUCKT - 1007222



Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

accessories

ZB 6:UNBEDRUCKT - 1051003



UC-TM 6 - 0818085



UCT-TM 6 - 0828736



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

accessories

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

accessories

End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442




E/UK 1 - 1201413




Drawings

Sensor/actuator terminal block - VIOK 1,5-2D - 2718196

Circuit diagram



Circuit diagram



1 = fixed bridge
2 = insertion bridge

