

## Data Sheet

## LED Day Light 2D

17611



**Designation:** 17611 101 421

**Battery Requirement:** 2x D

**Bulb required:** 7 pcs. Keetat 5mm white LED

**Luminous intensity:** 58 lumens or 1000 cd

**Range:** 63m (calculated distance at maximum luminous intensity with an illuminance of 0.25 lux)

**Weight:** 191g (without batteries)

**Material:**

Aluminum

ABS (Acrylonitrile Butadiene Styrene)

TPR (Thermoplastic Rubber)

HIPS (High impact Polystyrene)

PS (General purpose Polystyrene)

All contact parts made of bronze or nickel plated steel

Dimensions (mm):	A	196
	B	63
	C	45
	D	48

**Run Time:** 120 hours (with VARTA HE)

**Features**

7 pcs. super bright 5mm white LED

Push switch (on/off)

1 meter impact resistant

Lanyard

DC/DC regulator

Anti-roll feature

Soft and durable rubber and aluminum grip