

Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Cross section: 0.2 mm² - 4 mm², AWG: 24 - 12, Connection type: Screw connection, Width: 5.2 mm, Color: blue, Mounting type: NS 15, NS 35/7,5, NS 35/15

MBKKB 2,5-PV BU

Product Features

- ✓ Fixed bridges and test sockets can be used on both levels
- ✓ Space saving thanks to compact design and mounting option on a 15 mm DIN rail
- ✓ Clear arrangement thanks to marking of all terminal points
- ✓ Easy potential distribution thanks to standardized plug-in bridges

Key commercial data

package_quantity	50
GTIN	4017918021337

Technical data

General

Number of levels	2
Number of connections	4
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V2

General

Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	24 A (the maximum load current must not be exceeded by the total current of all connected conductors)
Nominal voltage U _N	500 V
Open side panel	ja
Number of positions	1

Dimensions

Width	5.2 mm
-------	--------

Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

Technical data

Dimensions

Length	62 mm
Height NS 35/7,5	48 mm
Height NS 35/15	55.5 mm
Height NS 32	55.5 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	1.5 mm ²
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm ²
Cross section with insertion bridge, solid max.	2.5 mm ²
Cross section with insertion bridge, stranded max.	2.5 mm ²
Connection method	Screw connection
Stripping length	7 mm
Internal cylindrical gage	A3
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

classifications

eCl@ss

eCl@ss 4.0	27141118
------------	----------

Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

classifications

eCl@ss

eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

Approval details

UL Recognized 	
Nominal voltage UN	300 V
Nominal current IN	20 A
mm²/AWG/kcmil	30-12

cUL Recognized 	
Nominal voltage UN	300 V
Nominal current IN	20 A
mm²/AWG/kcmil	30-12

Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

approvals



cULus Recognized  US

accessories

Partition plate

DP-MBKKB 2,5 - 1413065



TS-KK 3 SO - 2778534



End cover

D-MBKKB 2,5 BU - 1413081



Bridge

Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

accessories


FB-150 METER - 0201595



FBRNI 2-5 N - 3000175



FBRNI 3-5 N - 3000162



FBRNI 4-5 N - 3000159



FBRNI 10-5 N - 2770639



EB 2- 5 - 1401158



Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

accessories

EB 3- 5 - 1401145



EB 10- 5 - 1401132



Test plug terminal block

RPS - 0201647



Terminal marking

SBS 5:UNBEDRUCKT - 1007219



ZB 5 :UNBEDRUCKT - 1050004



Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

accessories

UC-TM 5 - 0818108



UCT-TM 5 - 0828734



Screwdriver tools

SZS 0,6X3,5 - 1205053



Mounting rail

NS 15 UNPERF 2000MM - 1401695



NS 15 PERF 2000MM - 1401682



Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

accessories

NS 15 AL PERF 2000MM - 1401763



NS 15 WH PERF 2000MM - 1204096



NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

accessories

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Labeled terminal marker

ZB 5 CUS - 0824962



Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

accessories

UC-TM 5 CUS - 0824581



UCT-TM 5 CUS - 0829595



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

accessories

E/MBK - 1401637



E/MK - 1421633



E/MK 1 - 1421659



E/UK - 1201442



E/UK 1 - 1201413



Test socket

Feed-through terminal block - MBKKB 2,5-PV BU - 1414132

accessories

PSBJ 3/13/4 - 0201304



PSB 3/10/4 - 0601292



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>