

Feed-through terminal block - UK 16 - 3006014

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Cross section: 0.5 mm² - 16 mm², AWG: 20 - 6, Width: 10.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15, NS 32

Key commercial data

package_quantity	50
GTIN	4017918091286

Technical data

General

Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V2

General

Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC / EN
Nominal current I _N	76 A
Nominal voltage U _N	800 V
Open side panel	ja

Dimensions

Width	10.2 mm
Length	42.5 mm
Height NS 35/7,5	54 mm
Height NS 35/15	61.5 mm
Height NS 32	59 mm

Connection data

Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	16 mm ²

Feed-through terminal block - UK 16 - 3006014

Technical data

Connection data

Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	6
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	10 mm ²
Min. AWG conductor cross section, stranded	20
Max. AWG conductor cross section, stranded	8
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	10 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	10 mm ²
2 conductors with same cross section, solid min.	0.5 mm ²
2 conductors with same cross section, solid max.	4 mm ²
2 conductors with same cross section, stranded min.	0.5 mm ²
2 conductors with same cross section, stranded max.	4 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	4 mm ²
Connection method	Screw connection
Stripping length	11 mm
Internal cylindrical gage	B 6
Screw thread	M4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

Feed-through terminal block - UK 16 - 3006014

classifications

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

CSA / UL Recognized / cUL Recognized / GOST / GL / BV / DNV / RS / KR / NK / GOST / cULus Recognized / BV /

Approval details

CSA 	
Nominal voltage UN	600 V
Nominal current IN	80 A
mm²/AWG/kcmil	24-6

UL Recognized 	
Nominal voltage UN	600 V
Nominal current IN	65 A
mm²/AWG/kcmil	24-6

cUL Recognized 	
Nominal voltage UN	600 V
Nominal current IN	65 A
mm²/AWG/kcmil	24-6

Feed-through terminal block - UK 16 - 3006014

approvals

GOST 

GL

BV

DNV

RS

KR

NK



cULus Recognized  US

accessories

End cover

D-UK 16 BU - 3006108



Feed-through terminal block - UK 16 - 3006014

accessories

D-UK 16 - 3006027



Warning label printed

WS 5-10 - 1004429



WS 4-10 - 1004225



Cover profile

EA 7 - 1024250



Short-circuit connector

KSS 10 - 0310541



Feed-through terminal block - UK 16 - 3006014

accessories

Bridge

STL 35/16 - 0204097



STL 16/10 - 0204518



FBI 2-10 - 0203483



FBI 10-10 - 0203276



EB 2-10 - 0203153



Feed-through terminal block - UK 16 - 3006014

accessories

EB 10-10 - 0203137



EB 3-10 - 0203328



SB 2-10/15 - 0203234



Partition plate

TS-K - 1302215



Partition plate

ATP-UK - 3003224



Mounting rail

Feed-through terminal block - UK 16 - 3006014

accessories

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



Feed-through terminal block - UK 16 - 3006014

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Feed-through terminal block - UK 16 - 3006014

accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



Feed-through terminal block - UK 16 - 3006014

accessories

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 10:UNBEDRUCKT - 1053001



Feed-through terminal block - UK 16 - 3006014

accessories

UC-TM 10 - 0818069



UCT-TM 10 - 0829142



Labeled terminal marker

ZB 10 CUS - 0824941



UC-TM 10 CUS - 0824605



UCT-TM 10 CUS - 0829623



End block

Feed-through terminal block - UK 16 - 3006014

accessories

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Test socket

Feed-through terminal block - UK 16 - 3006014

accessories

PSBJ 4/15/6 FARBLOS - 0303419



PSBJ 4/15/6 WH - 0303312



PSBJ 4/15/6 RD - 0303325



PSBJ 4/15/6 BU - 0303354



PSBJ 4/15/6 YE - 0303367



PSBJ 4/15/6 GN - 0303370



Feed-through terminal block - UK 16 - 3006014

accessories

PSBJ 4/15/6 VT - 0303383



PSBJ 4/15/6 GY - 0303396



PSBJ 4/15/6 BK - 0303406



PSB 4/7/6 - 0303299



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>