

Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Component terminal block, Connection type: Spring-cage connection, Cross section: 0.08 mm² - 4 mm², AWG: 28 - 12, Nominal current: 22 A, Nominal voltage: 250 V, Length: 67.5 mm, Width: 5.2 mm, Color: gray, Assembly: NS 35/7,5, NS 35/15

Product Features

- ✓ For more versions and versions for soldering in components yourself, visit phoenixcontact.net/products
- ✓ Double-level diode and LED terminal blocks perform a wide range of switching tasks

Key commercial data

package_quantity	50
GTIN	4017918183066

Technical data

General

Number of levels	2
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	26 A (with 4 mm ² conductor cross section)
Rated surge voltage	4 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal current I _N	22 A
Nominal voltage U _N	250 V
Open side panel	ja

Dimensions

Width	5.2 mm
Length	67.5 mm
Height NS 35/7,5	47.5 mm
Height NS 35/15	55 mm

Component terminal block - STTB 2,5-2DIO/O-UL/UR-UL - 3031584

Technical data

Connection data

Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	2.5 mm ²
Min. AWG conductor cross section, stranded	28
Max. AWG conductor cross section, stranded	16
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Connection method	Spring-cage connection
Stripping length	10 mm
Internal cylindrical gage	A3

classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141127
eCl@ss 6.0	27141127
eCl@ss 7.0	27141127
eCl@ss 8.0	27141127

ETIM

ETIM 2.0	EC000903
ETIM 3.0	EC000903
ETIM 4.0	EC000903
ETIM 5.0	EC000903

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410

Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

classifications

UNSPSC

UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

CSA / UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

Approval details

CSA 		
Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN		
mm²/AWG/kcmil	28-12	28-12

UL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	20 A	20 A	5 A
mm²/AWG/kcmil	28-12	28-12	28-12

cUL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	20 A	20 A	5 A
mm²/AWG/kcmil	28-12	28-12	28-12

GOST 			
--	--	--	--

			
---	--	--	--

Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

approvals

cULus Recognized  US

accessories

End cover

D-STTB 2,5 - 3030459



Partition plate

ATP-STTB 4 - 3030747



Screwdriver tools

SZF 1-0,6X3,5 - 1204517



Marker carriers

STP 5-2 - 0800967



Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

accessories

Documentation

ST-IL - 3039900



Bridge

FBS 20-5 - 3030226



FBS 10-5 - 3030213



FBS 5-5 - 3030190



FBS 4-5 - 3030187



Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

accessories

FBS 3-5 - 3030174



FBS 2-5 - 3030161



FBS 50-5 - 3038930



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

accessories

NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZBF 5:UNBEDRUCKT - 0808642



UC-TMF 5 - 0818153



UCT-TMF 5 - 0828744



Labeled terminal marker

Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

accessories

ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



UCT-TMF 5 CUS - 0829658



Insulating sleeve

ISH 2,5/0,2 - 3002843



ISH 2,5/0,5 - 3002856



Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

accessories

ISH 2,5/1,0 - 3002869



Test plug terminal block

PAI-4-N GY - 3032871



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Component terminal block - STTB 2,5-2DIO/O-UL/UR- UL - 3031584

accessories

E/UK - 1201442



E/UK 1 - 1201413



Drawings

Circuit diagram

