

Test disconnect terminal block - URTK 6 - 3026272

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Test disconnect terminal block, Connection method: Screw connection, Cross section: 0.5 mm² -10 mm² , AWG: 20 - 10, Width: 8.2 mm, Mounting type: NS 35/7,5, NS 35/15, NS 32, Color: gray

Product Features

- The URTK 6 test disconnect terminal block and the UGSK 6 slide-type terminal block were developed specifically for use in current transformer secondary circuits
- Can be fitted on both sides with fixed and switchable bridges as well as test sockets with 4 mm diameter

Key commercial data

package_quantity	50
GTIN	4017918168056

Technical data

General

Number of levels	1
Number of connections	2
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	41 A
Nominal voltage U _N	400 V
Open side panel	ja
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed
Finger protection	guaranteed
Surge voltage test setpoint	7.3 kV
Result of surge voltage test	Test passed
Power frequency withstand voltage setpoint	1.89 kV

Test disconnect terminal block - URTK 6 - 3026272

Technical data

General

Result of power-frequency withstand voltage test	Test passed
Checking the mechanical stability of terminal points (5 x conductor connection)	Test passed
Bending test rotation speed	10 rpm
Bending test turns	135
Bending test conductor cross section/weight	0.5 mm ² / 0.3 kg
Bending test conductor cross section/weight	6 mm ² / 1.4 kg
Bending test conductor cross section/weight	10 mm ² / 2 kg
Result of bending test	Test passed
Conductor cross section tensile test	0.5 mm ²
Tractive force setpoint	30 N
Conductor cross section tensile test	6 mm ²
Tractive force setpoint	80 N
Conductor cross section tensile test	10 mm ²
Tractive force setpoint	90 N
Tensile test result	Test passed
Tight fit on carrier	NS 32/NS 35
Setpoint	5 N
Result of tight fit test	Test passed
Requirements, voltage drop	≤ 6,4 mV
Result of voltage drop test	Test passed
Temperature-rise test	Test passed
Conductor cross section short circuit testing	6 mm ²
Short-time current	0.72 kA
Conductor cross section short circuit testing	10 mm ²
Short-time current	1.2 kA
Short circuit stability result	Test passed
Proof of thermal characteristics (needle flame) effective duration	30 s
Result of thermal test	Test passed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Static insulating material application in cold	-60 °C

Dimensions

Length	91 mm
Width	8.2 mm
Height NS 35/7,5	51 mm
Height NS 35/15	58.5 mm
Height NS 32	56 mm

Connection data

Note	Terminal point
------	----------------

Test disconnect terminal block - URTK 6 - 3026272

Technical data

Connection data

Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	10 mm ²
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	6 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	8
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	6 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	6 mm ²
2 conductors with same cross section, solid min.	0.5 mm ²
2 conductors with same cross section, solid max.	2.5 mm ²
2 conductors with same cross section, stranded min.	0.5 mm ²
2 conductors with same cross section, stranded max.	4 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	4 mm ²
Connection method	Screw connection
Stripping length	10 mm
Internal cylindrical gage	A5
Screw thread	M4
Tightening torque, min	1.2 Nm
Tightening torque max	1.4 Nm

classifications

eCl@ss

eCl@ss 4.0	27141126
eCl@ss 4.1	27141126
eCl@ss 5.0	27141126
eCl@ss 5.1	27141126
eCl@ss 6.0	27141126
eCl@ss 7.0	27141126
eCl@ss 8.0	27141126

ETIM

Test disconnect terminal block - URTK 6 - 3026272

classifications

ETIM

ETIM 2.0	EC000902
ETIM 3.0	EC000902
ETIM 4.0	EC000902
ETIM 5.0	EC000902

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

UL Recognized / cUL Recognized / GOST / PRS / GOST / cULus Recognized /

Approval details

UL Recognized	
Nominal voltage UN	300 V
Nominal current IN	50 A
mm ² /AWG/kcmil	26-8


cUL Recognized	
Nominal voltage UN	300 V
Nominal current IN	50 A
mm ² /AWG/kcmil	26-8

GOST

PRS

Test disconnect terminal block - URTK 6 - 3026272

approvals



accessories

End cover

D-URTK 6 - 3026340



Screwdriver tools

SZS 1,0X4,0 VDE - 1205066



SZS 0,6X3,5 - 1205053



Terminal marking

SBS 8:UNBEDRUCKT - 1007235



Test disconnect terminal block - URTK 6 - 3026272

accessories

ZB 8:UNBEDRUCKT - 1052002



UC-TM 8 - 0818072



UCT-TM 8 - 0828740



Short-circuit connector

KSSI 2-8 - 3000722



KSSI 4-8 - 3000735



Partition plate

Test disconnect terminal block - URTK 6 - 3026272

accessories

ATP-URTK/SP - 0311139



Switching lock

S-URTK/SP - 0311155



S-URTK/SP - 0311155



Cover profile

AP-ME METER - 3034361



APH-ME - 3034374



Test disconnect terminal block - URTK 6 - 3026272

accessories

APT-ME - 3034358



Bridge

FBRI 10-8 N - 2772080



SB 3-8-T - 3026492



SB 10-8-T SO - 3026395



SB 10-8-T - 3026382



Test disconnect terminal block - URTK 6 - 3026272

accessories

SB 4-8-T - 3026379



SB 2-8-T - 3026366



EB 3- 8/ST - 5020810



Mounting rail

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



Test disconnect terminal block - URTK 6 - 3026272

accessories

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



Test disconnect terminal block - URTK 6 - 3026272

accessories

NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



Test disconnect terminal block - URTK 6 - 3026272

accessories

NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



Test disconnect terminal block - URTK 6 - 3026272

accessories

NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Labeled terminal marker

ZB 8 CUS - 0825011



UC-TM 8 CUS - 0824597



UCT-TM 8 CUS - 0829616



End block

Test disconnect terminal block - URTK 6 - 3026272

accessories

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Test socket

Test disconnect terminal block - URTK 6 - 3026272

accessories

PSBJ-URTK 6 FARBLOS - 3026450



PSBJ-URTK 6 RD - 3026719



PSBJ-URTK 6 BU - 3026434



PSBJ-URTK 6 YE - 3026405



PSBJ-URTK 6 GN - 3026418



PSBJ-URTK 6 VT - 3026421



Test disconnect terminal block - URTK 6 - 3026272

accessories

PSBJ-URTK 6 GY - 3026612



PSBJ-URTK 6 BK - 3026447




PSBJ-URTK 6 BN - 3026971




Drawings

Circuit diagram



Test disconnect terminal block - URTK 6 - 3026272


Circuit diagram



a = open
1 = cover
2 = fixed bridge
3 = switch bar
4 = switching lock
5 = test plug socket
6 = short-circuit plug

Test disconnect terminal block - URTK 6 - 3026272


Schematic diagram



Three-phase transducer test set

Test disconnect terminal block - URTK 6 - 3026272

Schematic diagram



Three-phase linked transducer test set

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>