

Feed-through terminal block - UK 5 N RD - 3026696

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Cross section: 0.2 mm² - 6 mm², AWG: 24 - 10, Width: 6.2 mm, Color: red, Mounting type: NS 35/7,5, NS 35/15, NS 32



Key commercial data

package_quantity	50
GTIN	4017918441135

Technical data

General

Number of levels	1
Number of connections	2
Color	red
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	41 A (with 6 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	32 A
Nominal voltage U _N	800 V
Open side panel	ja

Dimensions

Width	6.2 mm
Length	42.5 mm
Height NS 35/7,5	47 mm
Height NS 35/15	54.5 mm
Height NS 32	52 mm

Feed-through terminal block - UK 5 N RD - 3026696

Technical data

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	6 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	10
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	4 mm ²
Min. AWG conductor cross section, stranded	24
Max. AWG conductor cross section, stranded	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	2.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
Cross section with insertion bridge, solid max.	4 mm ²
Cross section with insertion bridge, stranded max.	4 mm ²
Connection method	Screw connection
Stripping length	8 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.6 Nm
Tightening torque max	0.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120

Feed-through terminal block - UK 5 N RD - 3026696

classifications

eCl@ss

eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

IECEX / ATEX / FM approved / UL Recognized / GL / UL Recognized / CSA / UL Recognized / KEMA-KEUR / cUL Recognized / GOST / GL / DNV / RS / IECEE CB Scheme / GOST / cULus Recognized /

Approval details

IECEX	
Nominal voltage UN	550 V
Nominal current IN	33 A
mm ² /AWG/kcmil	0.2-6


ATEX	
Nominal voltage UN	550 V
Nominal current IN	37.5 A
mm ² /AWG/kcmil	0.2-6

FM approved	
Nominal voltage UN	600 V


Feed-through terminal block - UK 5 N RD - 3026696

approvals


Nominal current I _N	30 A
mm ² /AWG/kcmil	30-10

UL Recognized 


Nominal voltage U _N	600 V
Nominal current I _N	30 A
mm ² /AWG/kcmil	30-10

GL 


Nominal voltage U _N	690 V
Nominal current I _N	32.5 A
mm ² /AWG/kcmil	4



Nominal voltage U _N	600 V
Nominal current I _N	30 A
mm ² /AWG/kcmil	30-10

CSA 

Nominal voltage U _N	600 V
Nominal current I _N	40 A
mm ² /AWG/kcmil	28-10



Nominal voltage U _N	600 V
Nominal current I _N	30 A
mm ² /AWG/kcmil	30-10

Feed-through terminal block - UK 5 N RD - 3026696

approvals

KEMA-KEUR	
Nominal voltage UN	800 V
Nominal current IN	
mm ² /AWG/kcmil	4

cUL Recognized	
Nominal voltage UN	600 V
Nominal current IN	30 A
mm ² /AWG/kcmil	30-10

GOST

--

DNV

RS

IECEE CB Scheme	
Nominal voltage UN	800 V
Nominal current IN	
mm ² /AWG/kcmil	4

--

cULus Recognized

Feed-through terminal block - UK 5 N RD - 3026696

accessories

End cover

D-UK 4/10 - 3003020



Warning label printed

WS 5- 6 - 1004403



WS 4- 6 - 1004209



WS 3- 6 - 1004115



Mounting material

ZSR - 2303608



Feed-through terminal block - UK 5 N RD - 3026696

accessories

ZSR-EX - 0200017



Bridge

FB-150 METER - 0201595



STL 35/ 5 - 0204107



STL 10N/5N - 0204110



LB 10-6 BU - 0202280



Feed-through terminal block - UK 5 N RD - 3026696

accessories

LB 10-6 GY - 0202358



LB 100-6 GY - 0202345



LB 100-6 BU - 0202303



KB- 6-EX - 0201485



FB 100- 6 - 0201524



FBI 2- 6 - 0203438



Feed-through terminal block - UK 5 N RD - 3026696

accessories

FBI 10- 6 - 0203250



FB 3- 6-EX - 0201469



FB 2- 6-EX - 0201456



FB 5- 6 - 0201029



FBI 100- 6 - 0201650



Feed-through terminal block - UK 5 N RD - 3026696

accessories

FBI 20- 6 - 0201867



FB 10- 6-EX - 0201281



FB 10- 6 - 0201184



EB 2- 6 - 0201155



EB 3- 6 - 0201142



EB 10- 6 - 0201139



Feed-through terminal block - UK 5 N RD - 3026696

accessories

USBRJ 2-7 - 2305538



USBR 2-7 - 2303239



LB 100-6 RD - 0202316



LB 10-6 RD - 0202293



Cover profile

EA 5 - 1024014



Feed-through terminal block - UK 5 N RD - 3026696

accessories

EA 5-WS - 1024085



Short-circuit connector

KSS 3- 6 - 0309523



KSS 6 - 0301547



Test plug terminal block

PS-UK 2,5 B/Z-6 - 3001239



PS-UK 2,5 B/E - 3001132



Feed-through terminal block - UK 5 N RD - 3026696

accessories

RPS - 0201647



MPS-MT - 0201744



Partition plate

TS-K - 1302215



Partition plate

ATP-UK - 3003224



Terminal marking

SBS 6:UNBEDRUCKT - 1007222



Feed-through terminal block - UK 5 N RD - 3026696

accessories

ZB 6:UNBEDRUCKT - 1051003



UC-TM 6 - 0818085



UCT-TM 6 - 0828736



Insulating sleeve

IS-K 4 - 1302338



ISSBI 10- 6 - 0301505



Feed-through terminal block - UK 5 N RD - 3026696

accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



Feed-through terminal block - UK 5 N RD - 3026696

accessories

MPS-IH BK - 0201731



Mounting rail

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Feed-through terminal block - UK 5 N RD - 3026696

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



Feed-through terminal block - UK 5 N RD - 3026696

accessories

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



Feed-through terminal block - UK 5 N RD - 3026696

accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Feed-through terminal block - UK 5 N RD - 3026696

accessories

Labeled terminal marker

ZB 6 CUS - 0824992



UC-TM 6 CUS - 0824589



UCT-TM 6 CUS - 0829602



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



Feed-through terminal block - UK 5 N RD - 3026696

accessories

E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Test socket

PSBJ 3/13/4 - 0201304



PSB 3/10/4 - 0601292



Feed-through terminal block - UK 5 N RD - 3026696

accessories

FB 20- 6 - 0203506

FB 4- 6-EX - 0201443

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>