

Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Component terminal block, Connection method: Spring-cage connection, Cross section: 0.08 mm² - 4 mm², AWG: 28 - 12, Width: 5.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

Product Features

- ✓ 5.2 mm or 6.2 mm design width

Key commercial data

package_quantity	50
GTIN	4017918819286

Technical data

General

Number of levels	1
Number of connections	3
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	(the maximum current is determined by the diode)
Rated surge voltage	4 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal current I _N	0.5 A (the maximum current is determined by the diode)
Nominal voltage U _N	800 V
Open side panel	ja

Dimensions

Width	5.2 mm
Length	60.5 mm
Height NS 35/7,5	36.5 mm
Height NS 35/15	44 mm

Connection data

Conductor cross section solid min.	0.08 mm ²
------------------------------------	----------------------

Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

Technical data

Connection data

Conductor cross section solid max.	4 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	2.5 mm ²
Min. AWG conductor cross section, stranded	28
Max. AWG conductor cross section, stranded	14
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Connection method	Spring-cage connection
Minimum stripping length	8 mm
Maximum stripping length	10 mm
Internal cylindrical gage	A3

classifications

eCl@ss

eCl@ss 4.0	27141127
eCl@ss 4.1	27141127
eCl@ss 5.0	27141127
eCl@ss 5.1	27141127
eCl@ss 6.0	27141127
eCl@ss 7.0	27141127
eCl@ss 8.0	27141127

ETIM

ETIM 2.0	EC000903
ETIM 3.0	EC000903
ETIM 4.0	EC000903
ETIM 5.0	EC000903

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410

Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

classifications

UNSPSC

UNSPSC 13.2	39121410
--------------------	----------

approvals

CSA / UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

Approval details

CSA 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN		
mm²/AWG/kcmil	28-12	28-12

UL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	20 A	20 A
mm²/AWG/kcmil	28-12	28-12

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	20 A	20 A
mm²/AWG/kcmil	28-12	28-12

GOST 		
--	--	--

		
---	--	--

Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

approvals

cULus Recognized  US

accessories

End cover

DS-ST 2,5 - 3036602



D-ST 2,5-TWIN - 3030488



D-ST 2,5-TWIN-0,8 OG - 3030512



DP PS-5 - 3036725



Labeled terminal marker

Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

accessories

WST 2,5 - 3030941



ZB 5 CUS - 0824962



UC-TM 5 CUS - 0824581



UCT-TM 5 CUS - 0829595



ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

accessories

UCT-TMF 5 CUS - 0829658



Partition plate

ATP-ST-TWIN - 3030789



Screwdriver tools

SZF 1-0,6X3,5 - 1204517



Documentation

ST-IL - 3039900



Bridge

Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

accessories

FBS 20-5 - 3030226



FBS 10-5 - 3030213



FBS 5-5 - 3030190



FBS 4-5 - 3030187



FBS 3-5 - 3030174



FBS 2-5 - 3030161



Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

accessories

FBS 50-5 - 3038930



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

accessories

NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Terminal marking

Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

accessories

ZB 5 :UNBEDRUCKT - 1050004



UC-TM 5 - 0818108



UCT-TM 5 - 0828734



ZBF 5:UNBEDRUCKT - 0808642



UC-TMF 5 - 0818153



UCT-TMF 5 - 0828744



Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246

accessories

Insulating sleeve

ISH 2,5/0,2 - 3002843



ISH 2,5/0,5 - 3002856



ISH 2,5/1,0 - 3002869



Test plug terminal block

PAI-4 - 3030925



PS-5 - 3030983



Component terminal block - ST 2,5-TWIN-DIO/L-R - 3036246


accessories

PS-5/2,3MM RD - 3038723



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>