

# Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Fuse modular terminal block, Connection method: Screw connection, Cross section: 0.2 mm<sup>2</sup>- 4 mm<sup>2</sup>, AWG: 24 - 12, Nominal current: 6.3 A, Nominal voltage: 400 V, Width: 8.2 mm, Fuse type: G / 6,3 x 32, Fuse type: Glass, Mounting type: NS 35/7,5, NS 35/15, NS 32, Color: black

## Product Features

- Versions with LED
- Compact double-level fuse terminal block

## Key commercial data

package_quantity	50
GTIN	4017918838935

## Technical data

### General

Number of levels	2
Number of connections	4
Color	black
Insulating material	PA
Inflammability class according to UL 94	V0

### General

Fuse	G / 6,3 x 32
Fuse type	Glass
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-3
Nominal current I <sub>N</sub>	6.3 A
Nominal voltage U <sub>N</sub>	400 V
Open side panel	nein

### Dimensions

Width	8.2 mm
Length	86.5 mm

# Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

## Technical data

### Dimensions

Height NS 35/7,5	79 mm
Height NS 35/15	87 mm
Height NS 32	84 mm

### Connection data

Conductor cross section solid min.	0.2 mm <sup>2</sup>
Conductor cross section solid max.	4 mm <sup>2</sup>
Conductor cross section stranded min.	0.2 mm <sup>2</sup>
Conductor cross section stranded max.	4 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve max.	4 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm <sup>2</sup>
2 conductors with same cross section, solid min.	0.2 mm <sup>2</sup>
2 conductors with same cross section, solid max.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1.5 mm <sup>2</sup>
Connection method	Screw connection
Stripping length	8 mm
Internal cylindrical gage	A4
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.8 Nm

## classifications

### eCl@ss

eCl@ss 4.0	27141116
eCl@ss 4.1	27141116
eCl@ss 5.0	27141116
eCl@ss 5.1	27141116

# Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

## classifications

### eCl@ss

eCl@ss 6.0	27141116
eCl@ss 7.0	27141116
eCl@ss 8.0	27141116

### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000899
ETIM 4.0	EC000899
ETIM 5.0	EC000899

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## approvals

CSA / GOST / GOST /

### Approval details

Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	15 A
mm <sup>2</sup> /AWG/kcmil	28-10	28-10

--

--

## accessories

### Bridge

# Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

accessories

VS - 3004207



FBRI 10-8 N - 2772080



EBS 2- 8 - 3118151



EBS 3- 8 - 3118148



EBS 10- 8 - 3118135



**Terminal marking**

## Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

### accessories

SBS 8:UNBEDRUCKT - 1007235



ZB 8:UNBEDRUCKT - 1052002



UC-TM 8 - 0818072



UCT-TM 8 - 0828740



ZBF 8:UNBEDRUCKT - 0808781



## Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

### accessories

UC-TMF 8 - 0818137



UCT-TMF 8 - 0828748



### Screwdriver tools

SZS 0,6X3,5 - 1205053



### Mounting rail

NS 32 PERF 2000MM - 1201002



NS 32 UNPERF 2000MM - 1201015



## Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

### accessories

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



## Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

### accessories

NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730





## Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

### accessories

NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



## Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

### accessories

NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



### Labeled terminal marker

ZB 8 CUS - 0825011



## Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

### accessories

UC-TM 8 CUS - 0824597



UCT-TM 8 CUS - 0829616



ZBF 8 CUS - 0825030



UC-TMF 8 CUS - 0824654



UCT-TMF 8 CUS - 0829672



**End block**

## Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

### accessories

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442




E/UK 1 - 1201413



### Drawings

# Fuse modular terminal block - UKK 5-HESILED 24 (6,3X32) - 0711632

Circuit diagram



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>