

# Coupling - SC 2,5/ 2 - 3041312

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Coupling, Connection method: Spring-cage connection, Number of positions: 2, Cross section: 0.08 mm<sup>2</sup> - 4 mm<sup>2</sup>, AWG: 28 - 12, Width: 10.4 mm, Height: 18.8 mm, Color: gray

The illustration shows a 6-position version

## Product Features

- Standard strain relief can be used
- Tested for railway applications

## Key commercial data

package_quantity	50
GTIN	4017918922665

## Technical data

### General

Number of levels	1
Number of connections	1
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
Area of application	Mechanical engineering
Area of application	Plant engineering

### General

Maximum load current	24 A (with 2.5 mm <sup>2</sup> conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 61984
Nominal current I <sub>N</sub>	24 A
Nominal voltage U <sub>N</sub>	500 V
Open side panel	ja
Number of positions	2

# Coupling - SC 2,5/ 2 - 3041312

## Technical data

### Dimensions

<b>Width</b>	10.4 mm
<b>Length</b>	37.2 mm
<b>Height</b>	18.8 mm

### Connection data

<b>Conductor cross section solid min.</b>	0.08 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	4 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	28
<b>Conductor cross section AWG/kcmil max</b>	12
<b>Conductor cross section stranded min.</b>	0.08 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	2.5 mm <sup>2</sup>
<b>Min. AWG conductor cross section, stranded</b>	28
<b>Max. AWG conductor cross section, stranded</b>	14
<b>Conductor cross section stranded, with ferrule without plastic sleeve min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule without plastic sleeve max.</b>	2.5 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve max.</b>	2.5 mm <sup>2</sup>
<b>2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.</b>	0.5 mm <sup>2</sup>
<b>Connection method</b>	Spring-cage connection
<b>Stripping length</b>	10 mm
<b>Internal cylindrical gage</b>	A3

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	272607xx
<b>eCl@ss 4.1</b>	27260701
<b>eCl@ss 5.0</b>	27260701
<b>eCl@ss 5.1</b>	27260701
<b>eCl@ss 6.0</b>	27141120
<b>eCl@ss 7.0</b>	27141120
<b>eCl@ss 8.0</b>	27141120

### ETIM

<b>ETIM 2.0</b>	EC000897
<b>ETIM 3.0</b>	EC000897
<b>ETIM 4.0</b>	EC000897
<b>ETIM 5.0</b>	EC000897

### UNSPSC

# Coupling - SC 2,5/ 2 - 3041312

## classifications

### UNSPSC

<b>UNSPSC 6.01</b>	30211802
<b>UNSPSC 7.0901</b>	39121402
<b>UNSPSC 11</b>	39121402
<b>UNSPSC 12.01</b>	39121402
<b>UNSPSC 13.2</b>	39121402

## approvals

UL Recognized / cUL Recognized / GOST / LR / GL / BV / DNV / RS / GOST / cULus Recognized /

### Approval details

**UL Recognized**

Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	20 A	20 A
mm <sup>2</sup> /AWG/kcmil	26-12	26-12

**cUL Recognized**

Usegroups	B	C
Nominal voltage UN	300 V	300 V
Nominal current IN	20 A	20 A
mm <sup>2</sup> /AWG/kcmil	26-12	26-12

**GOST**

**LR**

**GL**


**BV**

**DNV**

**RS**

## Coupling - SC 2,5/ 2 - 3041312

approvals



accessories

**End cover**

D-SC 2,5 - 3042243



DP PS-5 - 3036725



**Mounting material**

PDZ/2 - 3040562



PDZ/4 - 3040575



## Coupling - SC 2,5/ 2 - 3041312

accessories

### Marker pen

B-STIFT - 1051993



X-PEN 0,35 - 0811228



### Screwdriver tools

SZF 1-0,6X3,5 - 1204517



### Terminal marking

ZBF 5:UNBEDRUCKT - 0808642



UC-TMF 5 - 0818153



## Coupling - SC 2,5/ 2 - 3041312

### accessories

UCT-TMF 5 - 0828744



### Labeled terminal marker

ZBF 5 CUS - 0825025



UC-TMF 5 CUS - 0824638



UCT-TMF 5 CUS - 0829658



### Test plug terminal block

MPS-MT - 0201744



## Coupling - SC 2,5/ 2 - 3041312

accessories

PS-5 - 3030983



PS-5/2,3MM RD - 3038723



**Insulating sleeve**

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



## Coupling - SC 2,5/ 2 - 3041312

### accessories

MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



ISH 2,5/0,2 - 3002843



ISH 2,5/0,5 - 3002856





# Coupling - SC 2,5/ 2 - 3041312

accessories

---

ISH 2,5/1,0 - 3002869



## Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>